

Nameplate Specifications

Phase	3	Output HP	500 & 400 Hp
Output KW	370.0 & 300.0 kW	Voltage	460 & 380 V
Speed	1780 & 1478 rpm	Service Factor	1.0 & 1.0
Frame	449TS	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	96.2 & 95.4 %
Ambient Temperature	50 °C	Frequency	60 & 50 Hz
Current	570 & 550 A	Power Factor	86
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	E
Drive End Bearing Size	6314	Opp Drive End Bearing Size	6314
UL	No	CSA	Y
CE	Y	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Part Wdg Start & Wye Start Delta Run
Poles	4	Rotation	Reversible
Resistance Main	.008 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	TS	Overall Length	44.50 in
Frame Length	29.38 in	Shaft Diameter	2.375 in
Shaft Extension	5 in	Assembly/Box Mounting	F1/F2 Capable
Connection Drawing	A-EE7300BH	Outline Drawing	B-SS514570-2938