

## Nameplate Specifications

|                        |                |                            |                             |
|------------------------|----------------|----------------------------|-----------------------------|
| Output HP              | 350 Hp         | Output KW                  | 260.0 kW                    |
| Frequency              | 60 Hz          | Voltage                    | 460 V                       |
| Current                | 373.0 A        | Speed                      | 3580 rpm                    |
| Service Factor         | 1.15           | Phase                      | 3                           |
| Efficiency             | 95.8 %         | Power Factor               | 91.8                        |
| Duty                   | Continuous     | Insulation Class           | H                           |
| Design Code            | B              | KVA Code                   | G                           |
| Frame                  | 449TS          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection  | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6314           | Opp Drive End Bearing Size | 6314                        |
| UL                     | Listed         | CSA                        | Y                           |
| CE                     | Y              | IP Code                    | 55                          |
| Hazardous Location     | DIVISION 2 T2B | Number of Speeds           | 1                           |

## Technical Specifications

|                       |                              |                   |                            |
|-----------------------|------------------------------|-------------------|----------------------------|
| Electrical Type       | Squirrel Cage Inverter Rated | Starting Method   | Line Or Inverter           |
| Poles                 | 2                            | Rotation          | Reversible                 |
| Resistance Main       | .00943 Ohms                  | Mounting          | Rigid Base                 |
| Motor Orientation     | Horizontal                   | Drive End Bearing | Ball                       |
| Opp Drive End Bearing | Ball                         | Frame Material    | Cast Iron                  |
| Shaft Type            | TS                           | Shaft Diameter    | 2.375 in                   |
| Assembly/Box Mounting | F1/F2 CAPABLE                | Inverter Load     | CONSTANT 2:1/VARIABLE 10:1 |
| Connection Drawing    | EE7300U                      | Outline Drawing   | SS557672                   |