

Nameplate Specifications

Output HP	450 Hp	Output KW	340.0 kW
Frequency	60 Hz	Voltage	460 V
Current	495.0 A	Speed	3572 rpm
Phase	3	Efficiency	95.8 %
Power Factor	89.5	Duty	NONE
Insulation Class	NONE	Design Code	NO DESIGN CODE
KVA Code	F	Frame	449TZ
Enclosure	Drip Proof	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	NONE
Opp Drive End Bearing Size	NONE	UL	No
CSA	N	CE	N
IP Code	12	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	NONE
Resistance Main	.0083 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Frame Material	Cast Iron
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS557257-2938	Connection Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/18/2022