

PRODUCT INFORMATION PACKET



Model No: 449TTDCD6077
Catalog No: GT00016
200,1200,DP,449T,3/60/460

Miscellaneous

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E








Nameplate Specifications

Technical Specifications

Outline Drawing	SS620758-200	Connection Drawing	EE7341A
-----------------	--------------	--------------------	---------


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/30/2021

DASH NO.	B	C	E	2E	2F	2FF	BA	BS	MOUNTING	FRAMES
100	25.20	44.57	9.00	18.00	14.50	16.50	7.50	12.99	F1 OR F2	444/445T
200	30.31	49.69			20.00	25.00		15.55		447/449T



DRAWING REVISION B	REVISION BY BISWA	REV DATE / @ DATE 10/03/2021
ECO CR-0001577	APPROVED BY GNK	DATE 10/03/2021
ECO DESCRIPTION DRAWING UPDATED		
<small> COPYRIGHT (PER REVISION DATE) REGAL BELLOIT AMERICA, INC. ALL RIGHTS RESERVED. IMPROVED PART AND COMPONENT INFORMATION. THIS DOCUMENT IS THE PROPERTY OF REGAL BELLOIT AMERICA, INC. (OWNER) AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSONAL INFORMATION OR OTHER DATA RECEIVED IS TO BE RECORDED IT TO AGREE THAT IT AND/OR ANY PART OF IT SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, UNLESS AND UNLESS, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS. </small>		


PRIMARY DIMENSIONS ARE INCH
 (MM DIMENSIONS IN BRACKET)
 ARE FOR REFERENCE ONLY

DRAWN BY ZXW	 Regal Beloit America, Inc.	DESCRIPTION OUTLINE 444/57/91 FR-NEMA ODP CAST IRON	
DATE 21/07/2016			
APPROVED BY	MATERIAL	PROCESS/FINISH	
DATE			
REFERENCE			
THIRD ANGLE PROJECTION	SIZE B	DRAWING NUMBER SS620758	SHEET 1 OF 1

THREE PHASE - PART WINDING START MOTOR
2 CKT Y - 6 LEADS - 6 POLE


START - CONNECT LINE 1 TO T1
CONNECT LINE 2 TO T2
CONNECT LINE 3 TO T3
OPEN T7, T8, AND T9

RUN - CONNECT LINE 1 TO T1 & T7
CONNECT LINE 2 TO T2 & T8
CONNECT LINE 3 TO T3 & T9



VIEWING TERMINAL END

SEE 7341P FOR PROTECTORS
SEE 7441S FOR SPACE HEATERS
SEE 7344 FOR A LEAD DUAL VOLTAGE

				✓ MAX. SURFACE ROUGHNESS UNLESS NOTED OTHERWISE	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL. ON XX± XXX±.005 XXXX±.0005 ANGLES±					
				MATL SPEC				DRAWN BY DRS	12-14-1998	
				FINISH	 WAUSAU, WISCONSIN 54401			CHKD BY MRB	12-14-1998	
3	12-14-1998	REDRAWN ON CADD	DRS					APPD BY GK	12-14-1998	
REV	DATE	CHANGE	NAME	PART NAME CONNECTION DIAGRAM - 3 PHASE 2 CKT Y - 6 LEADS - PART WINDING START - 6 POLE					DRWG NO A - EE7341A	
		SHOP BOOK	PURCHASED	DISTRIBUTION - WA - LB - WP - LM			CADD FILE NO.	EE7341A		

SHOP BOOK

PURCHASED

DISTRIBUTION - WA - LB - WP - LM

CADD FILE NO.

EE7341A