

Nameplate Specifications

Phase	3	Output HP	350 Hp
Output KW	260.0 kW	Voltage	460 V
Speed	1788 rpm	Service Factor	1.15
Frame	5009LCZ	Enclosure	Totally Enclosed Air Over
Thermal Protection	No Protection	Efficiency	96.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	385.0 A	Power Factor	88
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	6324	Opp Drive End Bearing Size	6318
UL	No	CSA	Y
CE	Y	IP Code	54
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	.0075 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS553944-4150	Connection Drawing	A-EE7300EH

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023