

**Nameplate Specifications**

Output HP	450 Hp	Output KW	340.0 kW
Frequency	60 Hz	Voltage	460 V
Current	486.0 A	Speed	1787 rpm
Service Factor	1.15	Phase	3
Efficiency	96.2 %	Power Factor	90.2
Duty	Continuous	Insulation Class	H
Design Code	B	KVA Code	G
Frame	5011L	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No	Ambient Temperature	40 °C
Drive End Bearing Size	6322	Opp Drive End Bearing Size	6319
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

**Technical Specifications**

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	4	Rotation	Selective Clockwise
Resistance Main	.0067 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	L	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	SS620972	Connection Drawing	EE7300CD

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021