

Nameplate Specifications

Output HP	1750 Hp	Output KW	1310.0 kW
Frequency	60 Hz	Voltage	2300/4000-4160 V
Current	380.0/218.0-210.0 A	Speed	3580 rpm
Service Factor	1.15	Phase	3
Efficiency	96.5 %	Power Factor	89.5
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	F
Frame	5810S	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6316	Opp Drive End Bearing Size	6316
UL	Recognized	CSA	Y
CE	N	IP Code	23
Number of Speeds	1		

Technical Specifications

Electrical Type	Bar Rotator Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Fixed Counterclockwise
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Cast Iron	Shaft Type	S
Shaft Diameter	2.875 in	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	MCA8259	Connection Drawing	EE7304AC

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/13/2023