

Nameplate Specifications

Phase	3	Output HP	150 Hp
Output KW	112.0 kW	Voltage	460 V
Speed	528 rpm	Service Factor	1
Frame	5011L	Enclosure	TEBC
Thermal Protection	Thermostat	Efficiency	94.1 %
Ambient Temperature	40 °C	Frequency	27 Hz
Current	175.0 A	Power Factor	85
Duty	Continuous	Insulation Class	H
Design Code	A	KVA Code	H
Drive End Bearing Size	6324	Opp Drive End Bearing Size	6318
UL	No	CSA	Y
CE	N	IP Code	54
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	6	Rotation	Reversible
Resistance Main	.02 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	L	Assembly/Box Mounting	F1/F2 CAPABLE
Inverter Load	CONSTANT 1000:1		
Outline Drawing	B-SS553555-4950	Connection Drawing	A-EE7300LE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023