

Nameplate Specifications

Phase	3	Output HP	350 Hp
Output KW	260.0 kW	Voltage	2300/4000 V
Speed	1190 rpm	Service Factor	1.15
Frame	5011LX	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	95.8 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	81.5/47.0 A	Power Factor	83
Duty	Continuous	Insulation Class	H
Design Code	B	KVA Code	G
Drive End Bearing Size	6324	Opp Drive End Bearing Size	6318
UL	No	CSA	Y
CE	N	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Resistance Main	.28 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	LX	Overall Length	73.80 in
Frame Length	49.50 in	Shaft Diameter	3.875 in
Shaft Extension	12.3 in	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS518707-4950	Connection Drawing	A-EE7304AC