

Nameplate Specifications

Output HP	450 Hp	Output KW	340.0 kW
Frequency	60 Hz	Voltage	460 V
Current	479.0 A	Speed	3582 rpm
Service Factor	1.15	Phase	3
Efficiency	95.8 %	Power Factor	91.7
Duty	Continuous	Insulation Class	H
Design Code	B	KVA Code	G
Frame	5011S	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No	Ambient Temperature	40 °C
Drive End Bearing Size	6314	Opp Drive End Bearing Size	6314
UL	Recognized	CSA	Y
CE	Y	IP Code	56
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	2	Rotation	Selective Clockwise
Resistance Main	.0048 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	S	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	EE7300CD	Outline Drawing	SS620971

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021