

Nameplate Specifications

Phase	3	Output HP	600 Hp
Output KW	450.0 kW	Voltage	420 V
Speed	650 rpm	Service Factor	1
Frame	6805L	Enclosure	DPFV
Thermal Protection	Thermostat	Efficiency	94.5 %
Ambient Temperature	50 °C	Frequency	22 Hz
Current	750.0 A	Power Factor	86
Duty	60 Minute	Insulation Class	H
Design Code	VERIFY	KVA Code	J
Drive End Bearing Size	6326	Opp Drive End Bearing Size	6326
UL	No	CSA	Y
CE	N	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Wye Start Delta Run Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	.0088 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	L	Assembly/Box Mounting	F2/F1 CAPABLE
Outline Drawing	B-SS553997-3400	Connection Drawing	A-EE7304AL

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/12/2023