

Nameplate Specifications

Output HP	1200 Hp	Output KW	900.0 kW
Frequency	60 Hz	Voltage	460 V
Current	1300.0 A	Speed	1788 rpm
Service Factor	1	Phase	3
Efficiency	97.2 %	Power Factor	88.5
Duty	Continuous	Insulation Class	H
Design Code	INV	KVA Code	H
Frame	6805TZ	Enclosure	DPFV
Thermal Protection	Thermostat	Ambient Temperature	40 °C
Drive End Bearing Size	6326	Opp Drive End Bearing Size	6326
UL	No	CSA	N
CE	N	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	4	Rotation	Reversible
Resistance Main	.0024 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Special Extension Both Sides	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS556166-3400	Connection Drawing	A-EE7300S

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/23/2022