

Nameplate Specifications

Phase	3	Output HP	600 Hp
Output KW	450.0 kW	Voltage	460 V
Speed	1788 rpm	Service Factor	1
Frame	6805L	Enclosure	DPFV
Thermal Protection	Thermostat	Efficiency	96.8 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	645.0 A	Power Factor	89
Duty	Continuous	Insulation Class	H
Design Code	INV	KVA Code	F
Drive End Bearing Size	6326	Opp Drive End Bearing Size	6318
UL	No	CSA	Y
CE	Y	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	4	Rotation	Reversible
Resistance Main	.0052 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	L	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	B-SS554344-3400	Connection Drawing	A-EE7300S

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/24/2024