


PRODUCT INFORMATION PACKET



Model No: 6RN100L08E34U243041

Catalog No: 6RN100L08E34U24@3041

0.75 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 750 rpm, D230/Y400V 50Hz, 100 Frame B5, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Efficiency Class	IE3
------------------	-----

Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Model No. 8-Pole cage motor 6RN 100 0,75kW D230V 50Hz IM3041-FF215

U (V)	Δ / Y Conn	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load FL 3/4FL 1/2FL	PF at __load FL 3/4FL 1/2FL	I _A /I _N [pu]	T _A /T _N [pu]	T _K /T _N [pu]
230	D	50	0,75	1	3,75	710	10,1	IE3	75,0	0,67	3,70	1,50	2,10
400	Y				2,1								

Motor type	6RN100L08E34
Enclosure	Totally Enclosed Fan Cooling
Frame Material	Cast iron
Frame size	100
Duty	S1
Voltage	230 V
Frequency	50 Hz
Power output	0,75 kW
Insulation class	F
Ambient temperature	-20 till 40 °C
Temperature rise	temp.rise acc. B (80K)
Temperature rise surface	
Altitude above sea level	1000 mtr
Hazardous area classification	Safe area

Rotor type	Cage motor
Bearing type	6306-2Z/C3WT

Type of grease	Unirex N3
----------------	-----------

Country of origin	CZ
-------------------	----

Voltage/Freq	Locked rotor Torque [% nom]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 230V 50Hz	150%	370%		210%	

NOTE


All performance values at rated voltage and frequency.
All performance parameters are subjected to standard tolerance as per IEC 60034-1
Voltage, Frequency are as per IEC60034-1
Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30

Degree of protection	IP55
Mounting type	IM3041-FF215
Cooling method	IC411
Motor weight - approx.	kg
Gross weight - approx.	kg

Vibration level	according IEC60034-14
-----------------	-----------------------

Direction of rotation	cw /ccw
-----------------------	---------




This is an uncontrolled copy, data can be changed anytime.

6RN100L08E34 8-pole 0,75kW D/Y 230/400V 50Hz S1 IC411 IE3



Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice