


# PRODUCT INFORMATION PACKET



Model No: 6RN112M02E36U46B3641-A

Catalog No: 6RN112M02E36U46B@3641-A

5.50 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 3000 rpm, D400/Y690V 50Hz,  
112M Frame B14, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications

Output HP	7.5 Hp	Output KW	5.5 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	10.40 A	Speed	2950 rpm
Service Factor	1	Phase	3
Efficiency	89.2 %	Power Factor	0.86
Duty	S1	Insulation Class	F
Frame	112M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6306-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6306-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

### Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	B14	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Outline Drawing	6RN112M02E36U46B3641-A		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Datasheet



Mors 1-5, 7151 MX Eibergen NL  
 www.rotor.nl tel.: +31 545 464640  
 sales@rotor.nl tel.: +31 545 464646

**Model No.** 2-Pole cage motor 6RN 112M 5,5kW D400V 50Hz IM3641-FT130

U (V)	Δ / Y Conn	f [Hz]	P		I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __load			I <sub>A</sub> /I <sub>N</sub> [pu]	T <sub>A</sub> /T <sub>N</sub> [pu]	T <sub>R</sub> /T <sub>N</sub> [pu]
			[kW]	[hp]					FL	3/4FL	1/2FL	FL	3/4FL	1/2FL			
400	D	50	5,5	7 1/3	10,4	2950	17,8	IE3	89,2	90,5	90,0	0,86	0,81	0,70	9,44	2,50	3,70
690	Y		6														
460	D	60	6,3	8,445	10	3550	16,9	IE3	91,1	90,5	89,4	0,87	0,82	0,75	10,20	2,62	3,98

Motor type	<b>6RN112M02E36</b>	Degree of protection	<b>IP55</b>
Enclosure	<b>Totally Enclosed Fan Cooling</b>	Mounting type	<b>IM3641-FT130</b>
Frame Material	<b>Cast iron</b>	Cooling method	<b>IC411</b>
Frame size	<b>112M</b>	Motor weight - approx.	<b>46 kg</b>
Duty	<b>S1</b>	Gross weight - approx.	<b>47 kg</b>
Voltage	<b>400 V</b>		
Frequency	<b>50 Hz</b>		
Power output	<b>5,5 kW</b>	Vibration level	<b>according IEC60034-14</b>
Insulation class	<b>F</b>		
Ambient temperature	<b>-20 till 40 °C</b>		
Temperature rise	<b>temp.rise acc. B (80K)</b>		
Temperature rise winding	<b>59 K</b>		
Temperature rise surface	<b>23 K</b>		
Altitude above sea level	<b>1000 mtr</b>	Direction of rotation	<b>cw / ccw</b>
Hazardous area classification	<b>Safe area</b>		

Rotor type	<b>Cage motor</b>
Bearing type	<b>6306-2Z/C3WT</b>
Type of grease	<b>Unirex N3</b>
Phase resistance at 20°C	<b>2,1928 Ohm</b>
Country of origin	<b>CZ</b>


Voltage/Freq	Locked rotor Torque [nom] [%]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 400V 50Hz	250%	944%	200%	370%	4,4 A
@ D 460V 60Hz	262%	1020%		398%	3,74 A

**NOTE**

All performance values at rated voltage and frequency.  
 All performance parameters are subjected to standard tolerance as per IEC 60034-1  
 Voltage, Frequency are as per IEC60034-1  
 Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30


This is an uncontrolled copy, data can be changed anytime.



6RN112M02E36 2-pole 5,50kW D/Y 400/690V 50Hz S1 IC411 IE3




Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice

Therm\_VSD graph



This is an uncontrolled copy - document subject to change - alterations reserved without notice