



Nameplate Specifications

Output HP	7.5 Hp	Output KW	5.5 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	10.40 A	Speed	2950 rpm
Service Factor	1	Phase	3
Efficiency	89.2 %	Power Factor	0.86
Duty	S1	Insulation Class	F
Frame	112M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6306-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6306-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	B14	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Outline Drawing	6RN112M02E36U46B3641-B		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023