


# PRODUCT INFORMATION PACKET

rotor nl®

Model No: 6RN132M04E32U46B2081-Uni

Catalog No: 6RN132M04E32U46B@2081-Uni

7.50 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 1500 rpm, D400/Y690V 50Hz,  
132M Frame B35, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



### Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	14.21 A	Speed	1465 rpm
Service Factor	1	Phase	3
Efficiency	90.4 %	Power Factor	0.84
Duty	S1	Insulation Class	F
Frame	132M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6308-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6308-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

### Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	B35	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	38 mm	Shaft Extension	80 mm
Outline Drawing	6RN132M04E32U46B2081-Uni		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022

**Model No.** 4-Pole cage motor 6RN 132M 7,5kW D400V 50Hz IM1081

U (V)	Δ/Y Conn	f [Hz]	P		I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __load			I <sub>A</sub> /I <sub>N</sub> [pu]	T <sub>A</sub> /T <sub>N</sub> [pu]	T <sub>K</sub> /T <sub>N</sub> [pu]
			[kW]	[hp]					FL	3/4FL	1/2FL	FL	3/4FL	1/2FL			
400	D	50	7,5	10	14,2	1465	48,6	IE3	90,9	91,3	90,6	0,84	0,80	0,71	8,20	2,44	3,46
690	Y		8,3														
460	D	60	8,6	11,53	14	1765	46,4	IE2	90,7	91,2	90,7	0,85	0,81	0,73	8,05	2,09	3,46

Motor type	<b>6RN132M04E32</b>
Enclosure	<b>Totally Enclosed Fan Cooling</b>
Frame Material	<b>Cast iron</b>
Frame size	<b>132M</b>
Duty	<b>S1</b>
Voltage	<b>400 V</b>
Frequency	<b>50 Hz</b>
Power output	<b>7,5 kW</b>
Insulation class	<b>F</b>
Ambient temperature	<b>-20 till 40 °C</b>
Temperature rise	<b>temp.rise acc. B (80K)</b>
Temperature rise winding	<b>46 K</b>
Temperature rise surface	<b>21 K</b>
Altitude above sea level	<b>1000 mtr</b>
Hazardous area classification	<b>Safe area</b>

Degree of protection	<b>IP55</b>
Mounting type	<b>IM1081</b>
Cooling method	<b>IC411</b>
Motor weight - approx.	<b>81 kg</b>
Gross weight - approx.	<b>83 kg</b>
Motor inertia	<b>0,0460 kgm<sup>2</sup></b>
Vibration level	<b>according IEC60034-14</b>

Rotor type	<b>Cage motor</b>
Bearing type	<b>6308-2Z/C3WT - 6308-2Z/C3WT</b>
Type of grease	<b>Unirex N3</b>


Phase resistance at 20°C	<b>1,4340 Ohm</b>
Country of origin	<b>CZ</b>

	Locked rotor Torque [nom]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 400V 50Hz	244%	816%	210%	346%	5,36 A
@ D 460V 60Hz	209%	807%	176%	346%	5,15 A


**NOTE**

All performance values at rated voltage and frequency.  
 All performance parameters are subjected to standard tolerance as per IEC 60034-1  
 Voltage, Frequency are as per IEC60034-1  
 Technical data are subject to change. There may be discrepancies between calculated and name plate values.


Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30



Torque versus Speed curve with variable frequency drive



Therm\_VSD graph



Tn graph

