

# PRODUCT INFORMATION PACKET



Model No: 6RN132M04E42U243041

Catalog No: 6RN132M04E42U24@3041

7.50 kW General Purpose Low Voltage IEC Motor IE4, 3 phase, 1500 rpm, D230/Y400V 50Hz,  
132M Frame B5, IC411

Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





## Nameplate Specifications

## Technical Specifications

---

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Datasheet



Mors 1-5, 7151 MX Eibergen NL  
 www.rotor.nl tel.: +31 545 464640  
 sales@rotor.nl tel.: +31 545 464646

**Model No.** 4-Pole cage motor 6RN 132M 7,5kW D230V 50Hz IM3041-FF265

U (V)	Δ/Y Conn	f [Hz]	P		I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __load			I <sub>A</sub> /I <sub>N</sub> [pu]	T <sub>A</sub> /T <sub>N</sub> [pu]	T <sub>R</sub> /T <sub>N</sub> [pu]
			[kW]	[hp]					FL	3/4FL	1/2FL	FL	3/4FL	1/2FL			
230	D	50	7,5	10	25,1	1467	48,8	IE3	91,6			0,82			8,99	2,98	3,98
400	Y				14,5												

Motor type	<b>6RN132M04E42</b>
Enclosure	<b>Totally Enclosed Fan Cooling</b>
Frame Material	<b>Cast iron</b>
Frame size	<b>132M</b>
Duty	<b>S1</b>
Voltage	<b>230 V</b>
Frequency	<b>50 Hz</b>
Power output	<b>7,5 kW</b>
Insulation class	<b>F</b>
Ambient temperature	<b>-20 till 40 °C</b>
Temperature rise	<b>temp.rise acc. B (80K)</b>
Temperature rise winding	<b>44 K</b>
Temperature rise surface	
Altitude above sea level	<b>1000 mtr</b>
Hazardous area classification	<b>Safe area</b>


Degree of protection	<b>IP55</b>
Mounting type	<b>IM3041-FF265</b>
Cooling method	<b>IC411</b>
Motor weight - approx.	<b>80 kg</b>
Gross weight - approx.	<b>82 kg</b>
Motor inertia	<b>0,0460 kgm<sup>2</sup></b>
Vibration level	<b>according IEC60034-14</b>
Direction of rotation	<b>cw / ccw</b>

Rotor type	<b>Cage motor</b>
Bearing type	<b>6308-2Z/C3WT</b>
Type of grease	<b>Unirex N3</b>
Country of origin	<b>CZ</b>

Locked rotor Torque [% nom]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
298%	900%	221%	398%	12,1 A

**NOTE**  
 All performance values at rated voltage and frequency.  
 All performance parameters are subjected to standard tolerance as per IEC 60034-1  
 Voltage, Frequency are as per IEC60034-1  
 Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30



V2.07


This is an uncontrolled copy, data can be changed anytime.



6RN132M04E42 4-pole 7,5kW D/Y 230/400V 50Hz S1 IC411 IE3




Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice

Therm\_VSD graph



This is an uncontrolled copy - document subject to change - alterations reserved without notice