



**Nameplate Specifications**

Output HP	5.50 Hp	Output KW	4.0 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	8.40 A	Speed	970 rpm
Service Factor	1	Phase	3
Efficiency	86.8 %	Power Factor	0.79
Duty	S1	Insulation Class	F
Frame	132M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6308-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6308-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

**Technical Specifications**

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	6	Rotation	Clockwise Shaft End
Mounting	B5	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	38 mm	Shaft Extension	80 mm
Outline Drawing	6RN132M06E32_3041		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023