


# PRODUCT INFORMATION PACKET



Model No: 6RN132S02E31U241081

Catalog No: 6RN132S02E31U24@1081

7.50 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 3000 rpm, D230/Y400V 50Hz,  
132S Frame B3, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





## Nameplate Specifications

|                        |                             |                            |                             |
|------------------------|-----------------------------|----------------------------|-----------------------------|
| Output HP              | 10 Hp                       | Output KW                  | 7.5 kW                      |
| Frequency              | 50 Hz                       | Voltage                    | D230/Y400 V                 |
| Current                | 22.57 A                     | Speed                      | 2950 rpm                    |
| Service Factor         | 1                           | Phase                      | 3                           |
| Efficiency             | 90.5 %                      | Power Factor               | 0.92                        |
| Duty                   | S1                          | Insulation Class           | F                           |
| Frame                  | 132S                        | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection               | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6308-2Z/C3WT (-40°C/+160°C) | Opp Drive End Bearing Size | 6308-2Z/C3WT (-40°C/+160°C) |
| UL                     | No                          | CSA                        | Optional                    |
| CE                     | Yes                         | IP Code                    | IP55                        |
| Number of Speeds       | 1                           | Efficiency Class           | IE3                         |

## Technical Specifications

|                 |                   |                   |                     |
|-----------------|-------------------|-------------------|---------------------|
| Electrical Type | Squirrel Cage     | Starting Method   | Direct On Line      |
| Poles           | 2                 | Rotation          | Clockwise Shaft End |
| Mounting        | B3                | Motor Orientation | Any                 |
| Frame Material  | Cast iron         | Shaft Type        | Keyed               |
| Shaft Diameter  | 38 mm             | Shaft Extension   | 80 mm               |
| Outline Drawing | 6RN132S02E31_1041 |                   |                     |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

## Datasheet

rotor nl®

rotor B.V.

Mors 1-5, 7151 MX Eibergen NL  
 www.rotor.nl tel.: +31 545 464640  
 sales@rotor.nl tel.: +31 545 464646

Model No. 2-Pole cage motor 6RN 132S 7,5kW D230V 50Hz IM1081

| U<br>(V) | Δ / Y<br>Conn | f<br>[Hz] | P<br>[kW] | P<br>[hp] | I<br>[A] | n<br>[RPM] | T<br>[Nm] | IE<br>Class | % EFF at __ load |       |       | PF at __load |       |       | I <sub>A</sub> /I <sub>N</sub><br>[pu] | T <sub>A</sub> /T <sub>N</sub><br>[pu] | T <sub>K</sub> /T <sub>N</sub><br>[pu] |
|----------|---------------|-----------|-----------|-----------|----------|------------|-----------|-------------|------------------|-------|-------|--------------|-------|-------|----------------------------------------|----------------------------------------|----------------------------------------|
|          |               |           |           |           |          |            |           |             | FL               | 3/4FL | 1/2FL | FL           | 3/4FL | 1/2FL |                                        |                                        |                                        |
| 230      | D             | 50        | 7,5       | 10        | 22,6     | 2950       | 24,2      | IE3         | 90,5             | 91,5  | 91,5  | 0,92         | 0,90  | 0,84  | 8,87                                   | 1,92                                   | 3,87                                   |
| 400      | Y             |           |           |           | 13       |            |           |             |                  |       |       |              |       |       |                                        |                                        |                                        |
| 265      | D             | 60        | 8,6       | 11,53     | 22,6     | 3550       | 23        | IE3         | 90,2             | 90,2  | 89,2  | 0,92         | 0,90  | 0,86  | 8,30                                   | 2,10                                   | 4,00                                   |
| 460      | Y             |           |           |           | 13       |            |           |             |                  |       |       |              |       |       |                                        |                                        |                                        |

|                               |                              |
|-------------------------------|------------------------------|
| Motor type                    | 6RN132S02E31                 |
| Enclosure                     | Totally Enclosed Fan Cooling |
| Frame Material                | Cast iron                    |
| Frame size                    | 132S                         |
| Duty                          | S1                           |
| Voltage                       | 230 V                        |
| Frequency                     | 50 Hz                        |
| Power output                  | 7,5 kW                       |
| Insulation class              | F                            |
| Ambient temperature           | -20 till 40 °C               |
| Temperature rise              | temp.rise acc. B (80K)       |
| Temperature rise winding      | 50 K                         |
| Temperature rise surface      |                              |
| Altitude above sea level      | 1000 mtr                     |
| Hazardous area classification | Safe area                    |

|              |              |
|--------------|--------------|
| Rotor type   | Cage motor   |
| Bearing type | 6308-2Z/C3WT |

|                |           |
|----------------|-----------|
| Type of grease | Unirex N3 |
|----------------|-----------|

|                          |            |
|--------------------------|------------|
| Phase resistance at 20°C | 0,6564 Ohm |
| Country of origin        | CZ         |

| Voltage/Freq  | Locked rotor<br>Torque<br>[% nom] | Starting<br>current<br>[% nom] | Pull-up<br>Torque<br>[% nom] | Breakdown<br>Torque<br>[% nom] | No-load<br>Current<br>[A] |
|---------------|-----------------------------------|--------------------------------|------------------------------|--------------------------------|---------------------------|
| @ D 230V 50Hz | 192%                              | 884%                           | 179%                         | 387%                           | 6,04 A                    |
| @ D 265V 60Hz | 210%                              | 827%                           | 194%                         | 400%                           | 8,25 A                    |

## NOTE

All performance values at rated voltage and frequency.

All performance parameters are subjected to standard tolerance as per IEC 60034-1

Voltage, Frequency are as per IEC60034-1

Technical data are subject to change. There may be discrepancies between calculated and name plate values.


|            |                  |               |
|------------|------------------|---------------|
| Efficiency | Europe           | Global IEC    |
| Standards  | EN-IEC: 60034-30 | IEC: 60034-30 |

This is an uncontrolled copy, data can be changed anytime.

|                                    |                         |
|------------------------------------|-------------------------|
| Degree of protection               | IP55                    |
| Mounting type                      | IM1081                  |
| Cooling method                     | IC411                   |
| Motor weight - approx.             | 72 kg                   |
| Gross weight - approx.             | 74 kg                   |
| Motor inertia                      | 0,0310 kgm <sup>2</sup> |
| Vibration level                    | according IEC60034-14   |
| Noise level (pressure) acc 60034-9 | 68 dB(A)                |

|                       |          |
|-----------------------|----------|
| Direction of rotation | cw / ccw |
|-----------------------|----------|

Schematic presentation of torque-speed curve




rotor  
is a  
**ISO 9001**  
certified  
company

RegalRexnord

6RN132S02E31 2-pole 7,5kW D/Y 230/400V 50Hz S1 IC411 IE3




Torque versus Speed curve with variable frequency drive




This is an uncontrolled copy - document subject to change - alterations reserved without notice

Therm\_VSD graph



This is an uncontrolled copy - document subject to change - alterations reserved without notice

Tn graph



This is an uncontrolled copy - document subject to change - alterations reserved without notice