

PRODUCT INFORMATION PACKET



Model No: 6RN132S06E40U463041

Catalog No: 6RN132S06E40U46@3041

3.00 kW General Purpose Low Voltage IEC Motor IE4, 3 phase, 1000 rpm, D400/Y690V 50Hz,
132S Frame B5, IC411

Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	4.00 Hp	Output KW	3.0 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	6.90 A	Speed	975 rpm
Service Factor	1	Phase	3
Efficiency	85.6 %	Power Factor	0.73
Duty	S1	Insulation Class	F
Frame	132S	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6308-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6308-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE4

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	6	Rotation	Clockwise Shaft End
Mounting	B5	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Datasheet



Mors 1-5, 7151 MX Eibergen NL
 www.rotor.nl tel.: +31 545 464640
 sales@rotor.nl tel.: +31 545 464646

Model No. 6-Pole cage motor 6RN 132S 3kW D400V 50Hz IM3041-FF265

U (V)	Δ/Y Conn	f [Hz]	P		I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __load			I _A /I _N [pu]	T _A /T _N [pu]	T _R /T _N [pu]
			[kW]	[hp]					FL	3/4FL	1/2FL	FL	3/4FL	1/2FL			
400	D	50	3	4	6,9	975	29	N/A	58,6	86,7	86,4	0,73	0,68	0,57	6,60	2,30	3,20
690	Y				12												

Motor type	6RN132S06E40	Degree of protection	IP55
Enclosure	Totally Enclosed Fan Cooling	Mounting type	IM3041-FF265
Frame Material	Cast iron	Cooling method	IC411
Frame size	132S	Motor weight - approx.	68 kg
Duty	S1	Gross weight - approx.	70 kg
Voltage	400 V		
Frequency	50 Hz		
Power output	3 kW	Vibration level	according IEC60034-14
Insulation class	F		
Ambient temperature	-20 till 40 °C		
Temperature rise	temp.rise acc. B (80K)		
Temperature rise surface		Direction of rotation	cw /ccw
Altitude above sea level	1000 mtr		
Hazardous area classification	Safe area		
Rotor type	Cage motor		
Bearing type	6308-2Z/C3WT		
Type of grease	Unirex N3		
Phase resistance at 20°C	3,7168 Ohm		
Country of origin	CZ		


Voltage/Freq	Locked rotor Torque [nom] [%]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 400V 50Hz	230%	659%		320%	

NOTE

All performance values at rated voltage and frequency.
 All performance parameters are subjected to standard tolerance as per IEC 60034-1
 Voltage, Frequency are as per IEC60034-1
 Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30


This is an uncontrolled copy, data can be changed anytime.



6RN132S06E40 6-pole 3,00kW D/Y 400/690V 50Hz S1 IC411



Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice