


# PRODUCT INFORMATION PACKET



Model No: 6RN160L04E36U461081

Catalog No: 6RN160L04E36U46@1081

18.50 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 1500 rpm, D400/Y690V 50Hz,  
160L Frame B3, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E






## Nameplate Specifications

|                        |                             |                            |                             |
|------------------------|-----------------------------|----------------------------|-----------------------------|
| Output HP              | 25 Hp                       | Output KW                  | 18.5 kW                     |
| Frequency              | 50 Hz                       | Voltage                    | D400/Y690 V                 |
| Current                | 35.50 A                     | Speed                      | 1475 rpm                    |
| Service Factor         | 1                           | Phase                      | 3                           |
| Efficiency             | 92.6 %                      | Power Factor               | 0.81                        |
| Duty                   | S1                          | Insulation Class           | F                           |
| Frame                  | 160L                        | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection               | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6309-2Z/C3WT (-40°C/+160°C) | Opp Drive End Bearing Size | 6309-2Z/C3WT (-40°C/+160°C) |
| UL                     | No                          | CSA                        | Optional                    |
| CE                     | Yes                         | IP Code                    | IP55                        |
| Number of Speeds       | 1                           | Efficiency Class           | IE3                         |

## Technical Specifications

|                 |                     |                   |                     |
|-----------------|---------------------|-------------------|---------------------|
| Electrical Type | Squirrel Cage       | Starting Method   | Direct On Line      |
| Poles           | 4                   | Rotation          | Clockwise Shaft End |
| Mounting        | B3                  | Motor Orientation | Any                 |
| Frame Material  | Cast iron           | Shaft Type        | Keyed               |
| Outline Drawing | 6RN160L04E36U461081 |                   |                     |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023



| REVISIONS |      |             |      |          | <div>REAL</div> <div>rotor</div> <div>Mors 2, P.O.box 45<br/>7150 AA Eibergen nl<br/>Tel:+31(0)545 464640<br/>E-mail: info@rotor.nl</div> | MOTORTYPE: 6RN160L04E36 |  | TITLE: Outline drawing |  | DRAWN:                                                                                                  |  | DATE:                                                                                            |  |
|-----------|------|-------------|------|----------|-------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|--|------------------------|--|---------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------|--|
| ZONE      | REV. | DESCRIPTION | DATE | APPROVED |                                                                                                                                           | MOUNTING: IM1041        |  | SPECIAL:               |  | CHECKED:                                                                                                |  | <div></div> |  |
|           |      |             |      |          |                                                                                                                                           | PROTECTION:             |  | ART. NR.:              |  | COMPLETE OR PARTIAL<br>COPYING OR USE OF<br>SPECIFICATIONS IS<br>NOT ALLOWED WITHOUT<br>OUR PERMISSION. |  |                                                                                                  |  |
|           |      |             |      |          |                                                                                                                                           | COOLING: IC411          |  | REVISION:              |  | SUBJECT TO ALTERATIONS                                                                                  |  |                                                                                                  |  |
|           |      |             |      |          |                                                                                                                                           | REMARKS:                |  | PAPER SIZE: A3         |  | PAGE 1 OF 1                                                                                             |  |                                                                                                  |  |
|           |      |             |      |          |                                                                                                                                           | DIMENSIONS: MM          |  | SCALE: 1: 5            |  |                                                                                                         |  |                                                                                                  |  |

## Datasheet

rotor nl®

rotor B.V.

Mors 1-5, 7151 MX Eibergen NL  
 www.rotor.nl tel.: +31 545 464640  
 sales@rotor.nl tel.: +31 545 464646

**Model No.** 4-Pole cage motor 6RN 160L 18,5kW D400V 50Hz IM1081

| U<br>(V) | Δ / Y<br>Conn | f<br>[Hz] | P<br>[kW] | P<br>[hp] | I<br>[A] | n<br>[RPM] | T<br>[Nm] | IE<br>Class | % EFF at __ load |       |       | PF at __load |       |       | I <sub>A</sub> /I <sub>N</sub><br>[pu] | T <sub>A</sub> /T <sub>N</sub><br>[pu] | T <sub>K</sub> /T <sub>N</sub><br>[pu] |
|----------|---------------|-----------|-----------|-----------|----------|------------|-----------|-------------|------------------|-------|-------|--------------|-------|-------|----------------------------------------|----------------------------------------|----------------------------------------|
|          |               |           |           |           |          |            |           |             | FL               | 3/4FL | 1/2FL | FL           | 3/4FL | 1/2FL |                                        |                                        |                                        |
| 400      | D             | 50        | 18,5      | 24,8      | 38       | 1475       | 120       | IE3         | 92,6             | 92,9  | 92,3  | 0,81         | 0,77  | 0,67  | 7,90                                   | 2,90                                   | 3,90                                   |
| 690      | Y             |           |           |           | 21       |            |           |             |                  |       |       |              |       |       |                                        |                                        |                                        |
| 460      | D             | 60        | 21,3      | 28,55     | 35       | 1775       | 115       | IE3         | 93,6             | 93,8  | 93,1  | 0,82         | 0,79  | 0,70  | 8,00                                   | 2,80                                   | 3,80                                   |

|                               |                              |
|-------------------------------|------------------------------|
| Motor type                    | 6RN160L04E36                 |
| Enclosure                     | Totally Enclosed Fan Cooling |
| Frame Material                | Cast iron                    |
| Frame size                    | 160L                         |
| Duty                          | S1                           |
| Voltage                       | 400 V                        |
| Frequency                     | 50 Hz                        |
| Power output                  | 18,5 kW                      |
| Insulation class              | F                            |
| Ambient temperature           | -20 till 40 °C               |
| Temperature rise              | temp.rise acc. B (80K)       |
| Temperature rise winding      | 58 K                         |
| Temperature rise surface      |                              |
| Altitude above sea level      | 1000 mtr                     |
| Hazardous area classification | Safe area                    |

|              |              |
|--------------|--------------|
| Rotor type   | Cage motor   |
| Bearing type | 6309-2Z/C3WT |

|                |           |
|----------------|-----------|
| Type of grease | Unirex N3 |
|----------------|-----------|

|                          |            |
|--------------------------|------------|
| Phase resistance at 20°C | 0,3517 Ohm |
| Country of origin        | CZ         |

| Voltage/Freq  | Locked rotor<br>Torque<br>[% nom] | Starting<br>current<br>[% nom] | Pull-up<br>Torque<br>[% nom] | Breakdown<br>Torque<br>[% nom] | No-load<br>Current<br>[A] |
|---------------|-----------------------------------|--------------------------------|------------------------------|--------------------------------|---------------------------|
| @ D 400V 50Hz | 290%                              | 736%                           |                              | 390%                           | 19,8 A                    |
| @ D 460V 60Hz | 280%                              | 800%                           |                              | 380%                           | 17,5 A                    |

## NOTE

All performance values at rated voltage and frequency.

All performance parameters are subjected to standard tolerance as per IEC 60034-1

Voltage, Frequency are as per IEC60034-1

Technical data are subject to change. There may be discrepancies between calculated and name plate values.


|            |                  |               |
|------------|------------------|---------------|
| Efficiency | Europe           | Global IEC    |
| Standards  | EN-IEC: 60034-30 | IEC: 60034-30 |

This is an uncontrolled copy, data can be changed anytime.

|                        |                         |
|------------------------|-------------------------|
| Degree of protection   | IP55                    |
| Mounting type          | IM1081                  |
| Cooling method         | IC411                   |
| Motor weight - approx. | 126 kg                  |
| Gross weight - approx. | 130 kg                  |
| Motor inertia          | 0,1010 kgm <sup>2</sup> |
| Vibration level        | according IEC60034-14   |

|                       |          |
|-----------------------|----------|
| Direction of rotation | cw / ccw |
|-----------------------|----------|

Schematic presentation of torque-speed curve




rotor  
is a  
**ISO 9001**  
certified  
company

RegalRexnord


6RN160L04E36 4-pole 18,50kW D/Y 400/690V 50Hz S1 IC411 IE3



Torque versus Speed curve with variable frequency drive



Therm\_VSD graph



This is an uncontrolled copy - document subject to change - alterations reserved without notice

Tn graph

