



Nameplate Specifications

Output HP	50.00 Hp	Output KW	37.0 kW
Frequency	50 Hz	Voltage	D230/Y400 V
Current	120.60 A	Speed	1475 rpm
Service Factor	1	Phase	3
Efficiency	93.9 %	Power Factor	0.81
Duty	S1	Insulation Class	F
Frame	200L	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6312-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6312-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	B3	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Outline Drawing	6RN200L04E36_1041		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023