

# PRODUCT INFORMATION PACKET



Model No: 6RN250M02E36U461041

Catalog No: 6RN250M02E36U46@1041

75.00 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 3000 rpm, D400/Y690V 50Hz,  
250M Frame B3, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E






## Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP              | 100 Hp        | Output KW                  | 75.0 kW                     |
| Frequency              | 50 Hz         | Voltage                    | D400/Y690 V                 |
| Current                | 127.00 A      | Speed                      | 2970 rpm                    |
| Service Factor         | 1             | Phase                      | 3                           |
| Efficiency             | 94.7 %        | Power Factor               | 0.90                        |
| Duty                   | S1            | Insulation Class           | F                           |
| Frame                  | 250M          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6315/C3       | Opp Drive End Bearing Size | 6315/C3                     |
| UL                     | No            | CSA                        | Optional                    |
| CE                     | Yes           | IP Code                    | IP55                        |
| Number of Speeds       | 1             | Efficiency Class           | IE3                         |

## Technical Specifications

|                 |                     |                   |                     |
|-----------------|---------------------|-------------------|---------------------|
| Electrical Type | Squirrel Cage       | Starting Method   | Direct On Line      |
| Poles           | 2                   | Rotation          | Clockwise Shaft End |
| Mounting        | B3                  | Motor Orientation | Any                 |
| Frame Material  | Cast iron           | Shaft Type        | Keyed               |
| Outline Drawing | 6RN250M02E36U461041 |                   |                     |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023



## Datasheet

rotor nl®

rotor B.V.

Mors 1-5, 7151 MX Eibergen NL  
 www.rotor.nl tel.: +31 545 464640  
 sales@rotor.nl tel.: +31 545 464646

Model No. 2-Pole cage motor 6RN 250M 75kW D400V 50Hz IM1041

| U<br>(V) | Δ / Y<br>Conn | f<br>[Hz] | P<br>[kW] | P<br>[hp] | I<br>[A] | n<br>[RPM] | T<br>[Nm] | IE<br>Class | % EFF at __ load |       |       | PF at __load |       |       | I <sub>A</sub> /I <sub>N</sub><br>[pu] | T <sub>A</sub> /T <sub>N</sub><br>[pu] | T <sub>K</sub> /T <sub>N</sub><br>[pu] |
|----------|---------------|-----------|-----------|-----------|----------|------------|-----------|-------------|------------------|-------|-------|--------------|-------|-------|----------------------------------------|----------------------------------------|----------------------------------------|
|          |               |           |           |           |          |            |           |             | FL               | 3/4FL | 1/2FL | FL           | 3/4FL | 1/2FL |                                        |                                        |                                        |
| 400      | D             | 50        | 75        | 100       | 127      | 2970       | 241       | IE3         | 94,7             | 94,9  | 94,5  | 0,90         | 0,89  | 0,83  | 6,80                                   | 2,14                                   | 2,86                                   |
| 690      | Y             |           |           |           | 74       |            |           |             |                  |       |       |              |       |       |                                        |                                        |                                        |
| 460      | D             | 60        | 84        | 112,6     | 123      | 3570       | 225       | IE3         | 95,0             | 94,5  | 94,3  | 0,90         | 0,89  | 0,84  | 6,80                                   | 2,30                                   | 2,90                                   |

|                |                              |
|----------------|------------------------------|
| Motor type     | 6RN250M02E36                 |
| Enclosure      | Totally Enclosed Fan Cooling |
| Frame Material | Cast iron                    |
| Frame size     | 250M                         |
| Duty           | S1                           |
| Voltage        | 400 V                        |
| Frequency      | 50 Hz                        |
| Power output   | 75 kW                        |

|                               |                        |
|-------------------------------|------------------------|
| Insulation class              | F                      |
| Ambient temperature           | -20 till 40 °C         |
| Temperature rise              | temp.rise acc. B (80K) |
| Temperature rise winding      | 66 K                   |
| Temperature rise surface      | 29 K                   |
| Altitude above sea level      | 1000 mtr               |
| Hazardous area classification | Safe area              |

|                    |              |
|--------------------|--------------|
| Rotor type         | Cage motor   |
| Bearing type       | 6315/C3      |
| Lubrication method | 25gr/4000hrs |
| Type of grease     | Unirex N3    |

|                   |    |
|-------------------|----|
| Country of origin | CZ |
|-------------------|----|

| Voltage/Freq  | Locked rotor<br>Torque<br>[% nom] | Starting<br>current<br>[% nom] | Pull-up<br>Torque<br>[% nom] | Breakdown<br>Torque<br>[% nom] | No-load<br>Current<br>[A] |
|---------------|-----------------------------------|--------------------------------|------------------------------|--------------------------------|---------------------------|
| @ D 400V 50Hz | 214%                              | 679%                           | 176%                         | 286%                           | 30 A                      |
| @ D 460V 60Hz | 230%                              | 679%                           |                              | 290%                           | 29 A                      |

## NOTE

All performance values at rated voltage and frequency.

All performance parameters are subjected to standard tolerance as per IEC 60034-1

Voltage, Frequency are as per IEC60034-1

Technical data are subject to change. There may be discrepancies between calculated and name plate values.


|            |                  |               |
|------------|------------------|---------------|
| Efficiency | Europe           | Global IEC    |
| Standards  | EN-IEC: 60034-30 | IEC: 60034-30 |

This is an uncontrolled copy, data can be changed anytime.

|                        |                         |
|------------------------|-------------------------|
| Degree of protection   | IP55                    |
| Mounting type          | IM1041                  |
| Cooling method         | IC411                   |
| Motor weight - approx. | 470 kg                  |
| Gross weight - approx. | 480 kg                  |
| Motor inertia          | 0,5600 kgm <sup>2</sup> |
| Vibration level        | according IEC60034-14   |

|                       |          |
|-----------------------|----------|
| Direction of rotation | cw / ccw |
|-----------------------|----------|

Schematic presentation of torque-speed curve




rotor  
is a  
**ISO 9001**  
certified  
company

RegalRexnord

6RN250M02E36 2-pole 75,00kW D/Y 400/690V 50Hz S1 IC411 IE3




Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice

Therm\_VSD graph



This is an uncontrolled copy - document subject to change - alterations reserved without notice