

PRODUCT INFORMATION PACKET

rotor nl®

Model No: 6RN200L06E35U46B2021-Uni

Catalog No: 6RN200L06E35U46B@2021-Uni

22.00 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 1000 rpm, D400/Y690V 50Hz,
200L Frame B35, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord®



Nameplate Specifications

Output HP	30.00 Hp	Output KW	22.0 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	44.15 A	Speed	978 rpm
Service Factor	1	Phase	3
Efficiency	93 %	Power Factor	0.78
Duty	S1	Insulation Class	F
Frame	200L	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6312-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6312-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	6	Rotation	Clockwise Shaft End
Mounting	B35	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	55 mm	Shaft Extension	110 mm
Outline Drawing	6RN200L06E35_1041		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022

Datasheet



rotor b.v.

Mors 1-5, 7151 MX Eibergen NL

www.rotor.nl tel.: +31 545 464640

sales@rotor.nl tel.: +31 545 464646

Model No. 6-Pole cage motor 6RN 200L 22kW D400V 50Hz IM2021-FF350

U (V)	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __ load			I _A /I _N [pu]	T _A /T _N [pu]	T _R /T _N [pu]
									FL	3/4FL	1/2FL	FL	3/4FL	1/2FL	0,78	0,74	0,64
400	D	50	22	30	44,1	978	214	IE3	92,0	92,7	92,5	0,78	0,74	0,64	5,60	2,32	2,62
690	Y				25,6												
460	D	60	22,4	30,03	38,4	1178	181	IE3	93,6	94,2	94,0	0,78	0,73	0,63	6,59	2,59	2,71

Motor type	6RN200L06E35	Degree of protection	IP55
Enclosure	Totally Enclosed Fan Cooling	Mounting type	IM2021-FF350
Frame Material	Cast iron	Cooling method	IC411
Frame size	200L	Motor weight - approx.	235 kg
Duty	S1	Gross weight - approx.	242 kg
Voltage	400 V	Motor inertia	0,3200 kgm ²
Frequency	50 Hz	Vibration level	according IEC60034-14
Power output	22 kW	Noise level (pressure) acc 60034-9	57 dB(A)
Insulation class	F		
Ambient temperature	-20 till 40 °C		
Temperature rise	temp.rise acc. B (80K)		
Temperature rise winding	60 K		
Temperature rise surface	32 K		
Altitude above sea level	1000 mtr	Direction of rotation	cw /ccw
Hazardous area classification	Safe area		
Rotor type	Cage motor		
Bearing type	6312-2Z/C3WT - 6312-2Z/C3WT		
Type of grease	Unirex N3		

Phase resistance at 20°C 0,3577 Ohm
Country of origin CZ

Voltage/Freq	Locked rotor Torque [% nom]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 400V 50Hz	232%	560%	200%	262%	18,6 A
@ D 460V 60Hz	259%	658%	190%	271%	17,3 A

NOTE


All performance values at rated voltage and frequency.

All performance parameters are subjected to standard tolerance as per IEC 60034-1

Voltage, Frequency are as per IEC60034-1

Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency Europe Global IEC
Standards EN-IEC: 60034-30 IEC: 60034-30




This is an uncontrolled copy, data can be changed anytime.

is a
ISO 9001
certified
company


6RN200L06E35 6-pole 22,00kW D/Y 400/690V 50Hz S1 IC411 IE3



Torque versus Speed curve with variable frequency drive



Therm_VSD graph



Tn graph

