

PRODUCT INFORMATION PACKET



Model No: 6RN280M08E32U461041

Catalog No: 6RN280M08E32U46@1041

45.00 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 750 rpm, D400/Y690V 50Hz,
280M Frame B3, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	60.00 Hp	Output KW	45.0 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	88.00 A	Speed	738 rpm
Service Factor	1	Phase	3
Efficiency	92.2 %	Power Factor	0.80
Duty	S1	Insulation Class	F
Frame	280M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6317/C3	Opp Drive End Bearing Size	6317/C3
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	8	Rotation	Clockwise Shaft End
Mounting	B3	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Model No. 8-Pole cage motor 6RN 280M 45kW D400V 50Hz IM1041

U (V)	Δ / Y Conn	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __load			I _A /I _N [pu]	T _A /T _N [pu]	T _K /T _N [pu]
FL	3/4FL	1/2FL	FL	3/4FL	1/2FL												
400	D	50	45	60,32	88	738	582	IE3	92,2	92,8	92,6	0,80	0,76	0,67	5,90	2,50	2,50
690	Y				50,8												

Motor type	6RN280M08E32
Enclosure	Totally Enclosed Fan Cooling
Frame Material	Cast iron
Frame size	280M
Duty	S1
Voltage	400 V
Frequency	50 Hz
Power output	45 kW
Insulation class	F
Ambient temperature	-20 till 40 °C
Temperature rise	temp.rise acc. B (80K)
Temperature rise surface	
Altitude above sea level	1000 mtr
Hazardous area classification	Safe area

Rotor type	Cage motor
Bearing type	6317/C3
Lubrication method	30gr/8000hrs
Type of grease	Unirex N3


Country of origin	CZ
-------------------	----

Voltage/Freq	Locked rotor Torque [nom] [%]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 400V 50Hz	250%	589%		250%	

NOTE
All performance values at rated voltage and frequency.
All performance parameters are subjected to standard tolerance as per IEC 60034-1
Voltage, Frequency are as per IEC60034-1
Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30

Degree of protection	IP55
Mounting type	IM1041
Cooling method	IC411
Motor weight - approx.	520 kg
Gross weight - approx.	540 kg
Motor inertia	1,4000 kgm²
Vibration level	according IEC60034-14
Direction of rotation	cw /ccw




This is an uncontrolled copy, data can be changed anytime.

6RN280M08E32 8-pole 45,00kW D/Y 400/690V 50Hz S1 IC411 IE3



Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice