

# PRODUCT INFORMATION PACKET



Model No: 6RN315L04E45U461041

Catalog No: 6RN315L04E45U46@1041

200.00 kW General Purpose Low Voltage IEC Motor IE4, 3 phase, 1500 rpm, D400/Y690V 50Hz,  
315L Frame B3, IC411

Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications

Output HP	270.00 Hp	Output KW	200.0 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	345.00 A	Speed	1491 rpm
Service Factor	1	Phase	3
Efficiency	96.7 %	Power Factor	0.86
Duty	S1	Insulation Class	F
Frame	315L	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6319/C3	Opp Drive End Bearing Size	6319/C3
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE4

### Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	B3	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Outline Drawing	6RN315L04E45_1041		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Datasheet



Mors 1-5, 7151 MX Eibergen NL  
 www.rotor.nl tel.: +31 545 464640  
 sales@rotor.nl tel.: +31 545 464646

**Model No.** 4-Pole cage motor 6RN 315L 200kW D400V 50Hz IM1041

U (V)	Δ/Y Conn	f [Hz]	P		I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __load			I <sub>A</sub> /I <sub>N</sub> [pu]	T <sub>A</sub> /T <sub>N</sub> [pu]	T <sub>R</sub> /T <sub>N</sub> [pu]
			[kW]	[hp]					FL	3/4FL	1/2FL	FL	3/4FL	1/2FL			
400	D	50	200	268,1	345	1491	1280	IE4	96,7			0,86			8,90	3,60	3,40
690	Y				200												
460	D	60	230	308,3	345	1790	1220	N/A	96,8			0,86			9,20	3,80	3,40

Motor type	<b>6RN315L04E45</b>
Enclosure	<b>Totally Enclosed Fan Cooling</b>
Frame Material	<b>Cast iron</b>
Frame size	<b>315L</b>
Duty	<b>S1</b>
Voltage	<b>400 V</b>
Frequency	<b>50 Hz</b>
Power output	<b>200 kW</b>
Insulation class	<b>F</b>
Ambient temperature	<b>-20 till 40 °C</b>
Temperature rise	<b>temp.rise acc. B (80K)</b>
Temperature rise surface	
Altitude above sea level	<b>1000 mtr</b>
Hazardous area classification	<b>Safe area</b>
Country of origin	<b>CZ</b>
Rotor type	<b>Cage motor</b>
Bearing type	<b>6319/C3</b>
Lubrication method	<b>40gr/6000hrs</b>
Type of grease	<b>Unirex N3</b>

Degree of protection	<b>IP55</b>
Mounting type	<b>IM1041</b>
Cooling method	<b>IC411</b>
Motor weight - approx.	<b>1310 kg</b>
Gross weight - approx.	<b>1350 kg</b>
Motor inertia	<b>4,4000 kgm<sup>2</sup></b>
Vibration level	<b>according IEC60034-14</b>
Direction of rotation	<b>cw / ccw</b>
	<b>PTC 150°C</b>


Voltage/Freq	Locked rotor Torque [nom] [%]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 400V 50Hz	360%	889%		340%	
@ D 460V 60Hz	380%	918%		340%	

**NOTE**

All performance values at rated voltage and frequency.  
 All performance parameters are subjected to standard tolerance as per IEC 60034-1  
 Voltage, Frequency are as per IEC60034-1  
 Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30


This is an uncontrolled copy, data can be changed anytime.



6RN315L04E45 4-pole 200,00kW D/Y 400/690V 50Hz S1 IC411 IE4



Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice