


# PRODUCT INFORMATION PACKET



Model No: 6RN225M06E42U463021

Catalog No: 6RN225M06E42U46@3021

30.00 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 1000 rpm, D400/Y690V 50Hz,  
225M Frame B5, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





## Nameplate Specifications

Output HP	40.00 Hp	Output KW	30.0 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	57.10 A	Speed	985 rpm
Service Factor	1	Phase	3
Efficiency	94.2 %	Power Factor	0.80
Duty	S1	Insulation Class	F
Frame	225M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6313/C3	Opp Drive End Bearing Size	6313/C3
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

## Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	6	Rotation	Clockwise Shaft End
Mounting	B5	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

## Datasheet

rotor nl®

rotor B.V.

Mors 1-5, 7151 MX Eibergen NL  
 www.rotor.nl tel.: +31 545 464640  
 sales@rotor.nl tel.: +31 545 464646

Model No. 6-Pole cage motor 6RN 225M 30kW D400V 50Hz IM3021-FF400

U (V)	Δ / Y Conn	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load FL 3/4FL 1/2FL	PF at __ load FL 3/4FL 1/2FL	I <sub>A</sub> /I <sub>N</sub> [pu]	T <sub>A</sub> /T <sub>N</sub> [pu]	T <sub>K</sub> /T <sub>N</sub> [pu]
400	D	50	30	40	57,1	985	291	IE4	94,2	0,80	8,13	3,12	3,40
690	Y				33								
460	D	60	36	48,26	58,5	1182	290	IE3	94,4	0,82	7,74	2,91	3,11

Motor type	6RN225M06E42
Enclosure	Totally Enclosed Fan Cooling
Frame Material	Cast iron
Frame size	225M
Duty	S1
Voltage	400 V
Frequency	50 Hz
Power output	30 kW
Insulation class	F
Ambient temperature	-20 till 40 °C
Temperature rise	temp.rise acc. B (80K)
Temperature rise winding	42 K
Temperature rise surface	24 K
Altitude above sea level	1000 mtr
Hazardous area classification	Safe area

Degree of protection	IP55
Mounting type	IM3021-FF400
Cooling method	IC411
Motor weight - approx.	290 kg
Gross weight - approx.	300 kg

Vibration level according IEC60034-14

Direction of rotation cw / ccw

Rotor type	Cage motor
Bearing type	6313/C3
Lubrication method	22gr/13400hrs
Type of grease	Unirex N3

Country of origin CZ

Voltage/Freq	Locked rotor Torque [% nom]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 400V 50Hz	312%	812%	276%	340%	23,3 A
@ D 460V 60Hz	291%	772%		311%	22,4 A

## NOTE


All performance values at rated voltage and frequency.

All performance parameters are subjected to standard tolerance as per IEC 60034-1

Voltage, Frequency are as per IEC60034-1

Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30



rotor  
is a  
**ISO 9001**  
certified  
company


This is an uncontrolled copy, data can be changed anytime.

RegalRexnord™

6RN225M06E42 6-pole 30,00kW D/Y 400/690V 50Hz S1 IC411 IE4




Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice

Therm\_VSD graph



This is an uncontrolled copy - document subject to change - alterations reserved without notice