


PRODUCT INFORMATION PACKET

rotor nl®

Model No: 6RN225S04E30U243021

Catalog No: 6RN225S04E30U24@3021

37.00 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 1500 rpm, D230/Y400V 50Hz,
225S Frame B5, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	50.00 Hp	Output KW	37.0 kW
Frequency	50 Hz	Voltage	D230/Y400 V
Current	117.00 A	Speed	1478 rpm
Service Factor	1	Phase	3
Efficiency	93.9 %	Power Factor	0.85
Duty	S1	Insulation Class	F
Frame	225S	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6313/C3	Opp Drive End Bearing Size	6313/C3
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	B5	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	60 mm	Shaft Extension	140 mm
Outline Drawing	6RN225S04E30_3021		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Datasheet



Mors 1-5, 7151 MX Eibergen NL
 www.rotor.nl tel.: +31 545 464640
 sales@rotor.nl tel.: +31 545 464646

Model No. 4-Pole cage motor 6RN 225S 37kW D230V 50Hz IM3021-FF400

U (V)	Δ/Y Conn	f [Hz]	P		I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __load			I _A /I _N [pu]	T _A /T _N [pu]	T _R /T _N [pu]
			[kW]	[hp]					FL	3/4FL	1/2FL	FL	3/4FL	1/2FL			
230	D	50	37	49,6	117	1478	239	IE3	93,8	94,4	94,3	0,85	0,81	0,72	6,55	2,43	2,64
400	Y		67,5														

Motor type	6RN225S04E30	Degree of protection	IP55
Enclosure	Totally Enclosed Fan Cooling	Mounting type	IM3021-FF400
Frame Material	Cast iron	Cooling method	IC411
Frame size	225S	Motor weight - approx.	290 kg
Duty	S1	Gross weight - approx.	300 kg
Voltage	230 V	Motor inertia	0,4200 kgm²
Frequency	50 Hz	Vibration level	according IEC60034-14
Power output	37 kW	Noise level (pressure) acc 60034-9	57 dB(A)
Insulation class	F		
Ambient temperature	-20 till 40 °C		
Temperature rise	temp.rise acc. B (80K)		
Temperature rise winding	58 K		
Temperature rise surface	33 K		
Altitude above sea level	1000 mtr	Direction of rotation	cw / ccw
Hazardous area classification	Safe area		

Rotor type	Cage motor
Bearing type	6313/C3
Lubrication method	22gr/10200hrs
Type of grease	Unirex N3
Phase resistance at 20°C	0,0570 Ohm
Country of origin	CZ


Voltage/Freq	Locked rotor Torque [nom] [%]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 230V 50Hz	243%	654%	224%	264%	40,7 A

NOTE

All performance values at rated voltage and frequency.
 All performance parameters are subjected to standard tolerance as per IEC 60034-1
 Voltage, Frequency are as per IEC60034-1
 Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30


This is an uncontrolled copy, data can be changed anytime.



6RN225S04E30 4-pole 37,00kW D/Y 230/400V 50Hz S1 IC411 IE3




Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice

Therm_VSD graph

This is an uncontrolled copy - document subject to change - alterations reserved without notice



Tn graph

