



Nameplate Specifications

Output HP	215.00 Hp	Output KW	160.0 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	294.00 A	Speed	991 rpm
Service Factor	1	Phase	3
Efficiency	95.6 %	Power Factor	0.82
Duty	S1	Insulation Class	F
Frame	315L	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6319/C3	Opp Drive End Bearing Size	6319/C3
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	6	Rotation	Clockwise Shaft End
Mounting	B3	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	80 mm	Shaft Extension	170 mm
Outline Drawing	6RN315L06E36_1041		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023