

# PRODUCT INFORMATION PACKET



Model No: 6RN250M04E42U46B2021

Catalog No: 6RN250M04E42U46B@2021

55.00 kW General Purpose Low Voltage IEC Motor IE4, 3 phase, 1500 rpm, D400/Y690V 50Hz,  
250M Frame B35, IC411

Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





## Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP              | 75.00 Hp      | Output KW                  | 55.0 kW                     |
| Frequency              | 50 Hz         | Voltage                    | D400/Y690 V                 |
| Current                | 96.60 A       | Speed                      | 1486 rpm                    |
| Service Factor         | 1             | Phase                      | 3                           |
| Efficiency             | 95.7 %        | Power Factor               | 0.86                        |
| Duty                   | S1            | Insulation Class           | F                           |
| Frame                  | 250M          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6315/C3       | Opp Drive End Bearing Size | 6315/C3                     |
| UL                     | No            | CSA                        | Optional                    |
| CE                     | Yes           | IP Code                    | IP55                        |
| Number of Speeds       | 1             | Efficiency Class           | IE4                         |

## Technical Specifications

|                 |                   |                   |                     |
|-----------------|-------------------|-------------------|---------------------|
| Electrical Type | Squirrel Cage     | Starting Method   | Direct On Line      |
| Poles           | 4                 | Rotation          | Clockwise Shaft End |
| Mounting        | B35               | Motor Orientation | Any                 |
| Frame Material  | Cast iron         | Shaft Type        | Keyed               |
| Outline Drawing | 6RN250M04E42_2041 |                   |                     |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

## Datasheet

rotor nl®

rotor B.V.

Mors 1-5, 7151 MX Eibergen NL  
 www.rotor.nl tel.: +31 545 464640  
 sales@rotor.nl tel.: +31 545 464646

Model No. 4-Pole cage motor 6RN 250M 55kW D400V 50Hz IM2021-FF500

| U<br>(V) | Δ / Y<br>Conn | f<br>[Hz] | P<br>[kW] | P<br>[hp] | I<br>[A] | n<br>[RPM] | T<br>[Nm] | IE<br>Class | % EFF at __ load |       |       | PF at __load |       |       | I <sub>A</sub> /I <sub>N</sub><br>[pu] | T <sub>A</sub> /T <sub>N</sub><br>[pu] | T <sub>K</sub> /T <sub>N</sub><br>[pu] |
|----------|---------------|-----------|-----------|-----------|----------|------------|-----------|-------------|------------------|-------|-------|--------------|-------|-------|----------------------------------------|----------------------------------------|----------------------------------------|
|          |               |           |           |           |          |            |           |             | FL               | 3/4FL | 1/2FL | FL           | 3/4FL | 1/2FL |                                        |                                        |                                        |
| 400      | D             | 50        | 55        | 75        | 96       | 1486       | 353       | IE4         | 95,8             | 95,9  | 95,5  | 0,86         | 0,82  | 0,73  | 8,37                                   | 2,95                                   | 3,35                                   |
| 690      | Y             |           |           |           | 55,4     |            |           |             |                  |       |       |              |       |       |                                        |                                        |                                        |
| 460      | D             | 60        | 63        | 84,45     | 96       | 1786       | 336       | IE4         | 95,9             | 96,0  | 95,6  | 0,86         | 0,83  | 0,74  | 8,34                                   | 2,88                                   | 3,17                                   |

|                |                              |
|----------------|------------------------------|
| Motor type     | 6RN250M04E42                 |
| Enclosure      | Totally Enclosed Fan Cooling |
| Frame Material | Cast iron                    |
| Frame size     | 250M                         |
| Duty           | S1                           |
| Voltage        | 400 V                        |
| Frequency      | 50 Hz                        |
| Power output   | 55 kW                        |

|                               |                        |
|-------------------------------|------------------------|
| Insulation class              | F                      |
| Ambient temperature           | -20 till 40 °C         |
| Temperature rise              | temp.rise acc. B (80K) |
| Temperature rise winding      | 51 K                   |
| Temperature rise surface      | 37 K                   |
| Altitude above sea level      | 1000 mtr               |
| Hazardous area classification | Safe area              |

|                    |              |
|--------------------|--------------|
| Rotor type         | Cage motor   |
| Bearing type       | 6315/C3      |
| Lubrication method | 25gr/8000hrs |
| Type of grease     | Unirex N3    |

|                          |            |
|--------------------------|------------|
| Phase resistance at 20°C | 0,0712 Ohm |
| Country of origin        | CZ         |

| Voltage/Freq  | Locked rotor<br>Torque<br>[% nom] | Starting<br>current<br>[% nom] | Pull-up<br>Torque<br>[% nom] | Breakdown<br>Torque<br>[% nom] | No-load<br>Current<br>[A] |
|---------------|-----------------------------------|--------------------------------|------------------------------|--------------------------------|---------------------------|
| @ D 400V 50Hz | 295%                              | 842%                           | 247%                         | 335%                           | 31 A                      |
| @ D 460V 60Hz | 288%                              | 830%                           | 231%                         | 317%                           | 30,4 A                    |

## NOTE

All performance values at rated voltage and frequency.

All performance parameters are subjected to standard tolerance as per IEC 60034-1

Voltage, Frequency are as per IEC60034-1


Technical data are subject to change. There may be discrepancies between calculated and name plate values.

|            |                  |               |
|------------|------------------|---------------|
| Efficiency | Europe           | Global IEC    |
| Standards  | EN-IEC: 60034-30 | IEC: 60034-30 |

|                                    |                         |
|------------------------------------|-------------------------|
| Degree of protection               | IP55                    |
| Mounting type                      | IM2021-FF500            |
| Cooling method                     | IC411                   |
| Motor weight - approx.             | 510 kg                  |
| Gross weight - approx.             | 530 kg                  |
| Motor inertia                      | 1,1000 kgm <sup>2</sup> |
| Vibration level                    | according IEC60034-14   |
| Noise level (pressure) acc 60034-9 | 67 dB(A)                |

|                       |          |
|-----------------------|----------|
| Direction of rotation | cw / ccw |
|-----------------------|----------|

Schematic presentation of torque-speed curve



rotor  
is a  
**ISO 9001**  
certified  
company


This is an uncontrolled copy, data can be changed anytime.

RegalRexnord


6RN250M04E42 4-pole 55,00kW D/Y 400/690V 50Hz S1 IC411 IE4



Torque versus Speed curve with variable frequency drive




Therm\_VSD graph



This is an uncontrolled copy - document subject to change - alterations reserved without notice

Tn graph



This is an uncontrolled copy - document subject to change - alterations reserved without notice