

PRODUCT INFORMATION PACKET



Model No: 6RN80M02E32U241081-Uni

Catalog No: 6RN80M02E32U24@1081-Uni

0.75 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 3000 rpm, D230/Y400V 50Hz,
80M Frame B3, IC411

Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1 Hp	Output KW	0.75 kW
Frequency	50 Hz	Voltage	D230/Y400 V
Current	2.75 A	Speed	2850 rpm
Service Factor	1	Phase	3
Efficiency	80.7 %	Power Factor	0.86
Duty	S1	Insulation Class	F
Frame	80M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6204-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6004-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	B3	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	19 mm	Shaft Extension	40 mm

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022


Model No. 2-Pole cage motor 6RN 80M 0,75kW D230V 50Hz IM1081

U (V)	Δ / Y Conn	f [Hz]	P		I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __ load			I _A /I _N [pu]	T _A /T _N [pu]	T _K /T _N [pu]
			[kW]	[hp]					FL	3/4FL	1/2FL	FL	3/4FL	1/2FL			
230	D	50	0,75	1	2,75	2850	2,5	IE3	80,7	82,0	81,5	0,86	0,82	0,73	6,20	2,60	3,00
400	Y				1,6												
265	D	60	0,86	1,153	2,85	3450	2,4	IE3	77,0	78,0	77,0	0,86	0,83	0,75	6,40	2,60	3,10
460	Y				1,65												

Motor type	6RN80M02E32
Enclosure	Totally Enclosed Fan Cooling
Frame Material	Cast iron
Frame size	80M
Duty	S1
Voltage	230 V
Frequency	50 Hz
Power output	0,75 kW
Insulation class	F
Ambient temperature	-20 till 40 °C
Temperature rise winding	62 K
Temperature rise surface	21 K
Altitude above sea level	1000 mtr
Hazardous area classification	Safe area
Rotor type	Cage motor
Bearing type	Rolling element bearing 6204-2Z/C3WT - 6004-2Z/C3WT
Type of grease	Unirex N3
Phase resistance at 20°C	11,8700 Ohm
Country of origin	CZ

Torques	Locked rotor	At start	Pull-up	Breakdown	No-load
@230V 50Hz	260%	6,5 A	200%	300%	1,4 A
@265V 60Hz	260%	7,38 A		310%	1,3 A

Degree of protection	IP55
Mounting type	IM1081
Cooling method	IC411
Motor weight - approx.	11 kg
Gross weight - approx.	11 kg
Motor inertia	0,0011 kgm²
Vibration level	according IEC60034-14
Starting method	d.o.l.
Direction of rotation	cw /ccw
Paint shade	RAL 7030
Terminal box position	Top - Pos 3



NOTE

All performance values at rated voltage and frequency.
 All performance parameters are subjected to standard tolerance as per IEC 60034-1
 Voltage, Frequency are as per IEC60034-1
 Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30




This is an uncontrolled copy, data can be changed anytime.




6RN80M02E32 2-pole 0,75kW D/Y 230/400V 50Hz S1 IC411 IE3



Torque versus Speed curve with variable frequency drive



Therm_VSD graph



Tn graph

