

PRODUCT INFORMATION PACKET



Model No: 6RN315L02E44U461041

Catalog No: 6RN315L02E44U46@1041

160.00 kW General Purpose Low Voltage IEC Motor IE4, 3 phase, 3000 rpm, D400/Y690V 50Hz,
3154 Frame B3, IC411

Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	215.00 Hp	Output KW	160.0 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	260.00 A	Speed	2988 rpm
Service Factor	1	Phase	3
Efficiency	96.3 %	Power Factor	0.92
Duty	S1	Insulation Class	F
Frame	3154	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6316/C3	Opp Drive End Bearing Size	6316/C3
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE4

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	B3	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Outline Drawing	6RN315L02E44_1041		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Datasheet

rotor nl®

rotor B.V.

Mors 1-5, 7151 MX Eibergen NL
 www.rotor.nl tel.: +31 545 464640
 sales@rotor.nl tel.: +31 545 464646

Model No. 2-Pole cage motor 6RN 3154 160kW D400V 50Hz IM1041

U (V)	Δ / Y Conn	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __load			I _A /I _N [pu]	T _A /T _N [pu]	T _K /T _N [pu]
									FL	3/4FL	1/2FL	FL	3/4FL	1/2FL			
400	D	50	160	214,5	260	2988	511	IE4	96,3	96,3	95,8	0,92	0,91	0,87	10,30	3,20	3,90
690	Y				152												
460	D	60	180	241,3	260	3588	479	IE4	96,2	96,2	95,6	0,91	0,90	0,87	11,20	3,30	4,10

Motor type	6RN315L02E44
Enclosure	Totally Enclosed Fan Cooling
Frame Material	Cast iron
Frame size	3154
Duty	S1
Voltage	400 V
Frequency	50 Hz
Power output	160 kW

Insulation class	F
Ambient temperature	-20 till 40 °C
Temperature rise	temp.rise acc. B (80K)

Temperature rise surface	
Altitude above sea level	1000 mtr
Hazardous area classification	Safe area

Rotor type	Cage motor
Bearing type	6316/C3
Lubrication method	30gr/3000hrs
Type of grease	Unirex N3

Country of origin	CZ
-------------------	----

Voltage/Freq	Locked rotor Torque [% nom]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 400V 50Hz	320%	1026%		390%	
@ D 460V 60Hz	330%	1119%		410%	

NOTE

All performance values at rated voltage and frequency.

All performance parameters are subjected to standard tolerance as per IEC 60034-1

Voltage, Frequency are as per IEC60034-1

Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30

This is an uncontrolled copy, data can be changed anytime.


Degree of protection	IP55
Mounting type	IM1041
Cooling method	IC411
Motor weight - approx.	1040 kg
Gross weight - approx.	1070 kg
Motor inertia	2,1000 kgm ²

Vibration level according IEC60034-14

Direction of rotation cw /ccw

PTC 150°C

Schematic presentation of torque-speed curve



rotor
is a
ISO 9001
certified
company

RegalRexnord

6RN315L02E44 2-pole 160,00kW D/Y 400/690V 50Hz S1 IC411 IE4



Torque versus Speed curve with variable frequency drive

