

PRODUCT INFORMATION PACKET

rotor nl[®]

Model No: 6RN80M04E32U461081

Catalog No: 6RN80M04E32U46@1081

0.55 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 1500 rpm, D400/Y690V 50Hz,
80M Frame B3, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	0.75 Hp	Output KW	0.55 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	1.25 A	Speed	1440 rpm
Service Factor	1	Phase	3
Efficiency	80.8 %	Power Factor	0.77
Duty	S1	Insulation Class	F
Frame	80M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6204-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6004-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	B3	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	19 mm	Shaft Extension	40 mm
Outline Drawing	6RN80M04E32_1041		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Datasheet



Mors 1-5, 7151 MX Eibergen NL
 www.rotor.nl tel.: +31 545 464640
 sales@rotor.nl tel.: +31 545 464646

Model No. 4-Pole cage motor 6RN 80M 0,55kW D400V 50Hz IM1081

U (V)	Δ / Y Conn	f [Hz]	P		I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __load			I _A /I _N [pu]	T _A /T _N [pu]	T _R /T _N [pu]
			[kW]	[hp]					FL	3/4FL	1/2FL	FL	3/4FL	1/2FL			
400	D	50	0,55	0,737	1,25	1440	3,65	IE3	81,5	81,8	79,9	0,77	0,69	0,56	3,45	2,13	3,10
690	Y				0,72												
460	D	60	0,63	0,845	1,23	1740	3,46	IE3	83,3	83,5	81,5	0,77	0,69	0,57	6,39	2,40	3,30
	Y																

Motor type	6RN80M04E32
Enclosure	Totally Enclosed Fan Cooling
Frame Material	Aluminum
Frame size	80M
Duty	S1
Voltage	400 V
Frequency	50 Hz
Power output	0,55 kW
Insulation class	F
Ambient temperature	-20 till 40 °C
Temperature rise	temp.rise acc. B (80K)
Temperature rise winding	23 K
Temperature rise surface	17 K
Altitude above sea level	1000 mtr
Hazardous area classification	Safe area

Degree of protection	IP55
Mounting type	IM1081
Cooling method	IC411
Motor weight - approx.	11 kg
Gross weight - approx.	11 kg
Motor inertia	0,0021 kgm²
Vibration level	according IEC60034-14
Noise level (pressure) acc 60034-9	50,3 dB(A)


Rotor type	Cage motor
Bearing type	6004-2Z/C3WT
Type of grease	Unirex N3
Country of origin	CZ

Voltage/Freq	Locked rotor Torque [nom] [%]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 400V 50Hz	213%	344%	210%	310%	0,76 A
@ D 460V 60Hz	240%	634%	204%	330%	0,71 A

NOTE

All performance values at rated voltage and frequency.
 All performance parameters are subjected to standard tolerance as per IEC 60034-1
 Voltage, Frequency are as per IEC60034-1
 Technical data are subject to change. There may be discrepancies between calculated and name plate values.

Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30




This is an uncontrolled copy, data can be changed anytime.



6RN80M04E32 4-pole 0,55kW D/Y 400/690V 50Hz S1 IC411 IE3




Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice

Therm_VSD graph



This is an uncontrolled copy - document subject to change - alterations reserved without notice