


PRODUCT INFORMATION PACKET

rotor nl®

Model No: 6RN80M04E36U243041

Catalog No: 6RN80M04E36U24@3041

1.10 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 1500 rpm, D230/Y400V 50Hz, 80 Frame B5, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Datasheet



Mors 1-5, 7151 MX Eibergen NL
 www.rotor.nl tel.: +31 545 464640
 sales@rotor.nl tel.: +31 545 464646

Model No. 4-Pole cage motor 6RN 80 1,1kW D230V 50Hz IM3041-FF165

| U (V) | Δ/Y Conn | f [Hz] | P | | I [A] | n [RPM] | T [Nm] | IE Class | % EFF at __ load | | | PF at __load | | | I _A /I _N [pu] | T _A /T _N [pu] | T _R /T _N [pu] |
|----------|-------------|-----------|------|-------|----------|------------|-----------|-------------|------------------|-------|-------|--------------|-------|-------|--|--|--|
| | | | [kW] | [hp] | | | | | FL | 3/4FL | 1/2FL | FL | 3/4FL | 1/2FL | | | |
| 230 | D | 50 | 1,1 | 1 1/2 | 4,2 | 1445 | 7,3 | IE3 | 84,1 | | | 0,78 | | | 7,00 | 3,00 | 3,50 |
| 400 | Y | | | | 2,4 | | | | | | | | | | | | |
| 265 | D | 60 | 1,27 | 1,702 | 4,08 | 1745 | 6,96 | IE3 | 86,5 | | | 0,79 | | | 7,75 | 3,00 | 3,75 |
| 460 | Y | | | | 2,35 | | | | | | | | | | | | |

| | |
|-------------------------------|------------------------------|
| Motor type | 6RN80M04E36 |
| Enclosure | Totally Enclosed Fan Cooling |
| Frame Material | Aluminum |
| Frame size | 80 |
| Duty | S1 |
| Voltage | 230 V |
| Frequency | 50 Hz |
| Power output | 1,1 kW |
| Insulation class | F |
| Ambient temperature | -20 till 40 °C |
| Temperature rise | temp.rise acc. B (80K) |
| Temperature rise surface | |
| Altitude above sea level | 1000 mtr |
| Hazardous area classification | Safe area |

| | |
|-------------------|--------------|
| Rotor type | Cage motor |
| Bearing type | 6004-2Z/C3WT |
| Type of grease | Unirex N3 |
| Country of origin | CZ |


| Voltage/Freq | Locked rotor Torque [% nom] | Starting current [% nom] | Pull-up Torque [% nom] | Breakdown Torque [% nom] | No-load Current [A] |
|---------------|-----------------------------------|--------------------------------|------------------------------|--------------------------------|---------------------------|
| @ D 230V 50Hz | 300% | 700% | | 350% | |
| @ D 265V 60Hz | 300% | 774% | | 375% | 2,11 A |

NOTE
 All performance values at rated voltage and frequency.
 All performance parameters are subjected to standard tolerance as per IEC 60034-1
 Voltage, Frequency are as per IEC60034-1
 Technical data are subject to change. There may be discrepancies between calculated and name plate values.

| | | |
|------------|------------------|---------------|
| Efficiency | Europe | Global IEC |
| Standards | EN-IEC: 60034-30 | IEC: 60034-30 |

This is an uncontrolled copy, data can be changed anytime.


| | |
|------------------------|-----------------------|
| Degree of protection | IP55 |
| Mounting type | IM3041-FF165 |
| Cooling method | IC411 |
| Motor weight - approx. | 17 kg |
| Gross weight - approx. | 18 kg |
| Vibration level | according IEC60034-14 |
| Direction of rotation | cw /ccw |



6RN80M04E36 4-pole 1,10kW D/Y 230/400V 50Hz S1 IC411 IE3



Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice