


# PRODUCT INFORMATION PACKET



Model No: 6RN90L02E34U24B2181-A

Catalog No: 6RN90L02E34U24B@2181-A

2.20 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 3000 rpm, D230/Y400V 50Hz,  
90L Frame B34, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications

Output HP	3.00 Hp	Output KW	2.2 kW
Frequency	50 Hz	Voltage	D230/Y400 V
Current	7.31 A	Speed	2920 rpm
Service Factor	1	Phase	3
Efficiency	85.9 %	Power Factor	0.88
Duty	S1	Insulation Class	F
Frame	90L	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6205-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6004-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

### Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	B34	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	24 mm	Shaft Extension	50 mm
Outline Drawing	6RN90L02E34_2141-A		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

Datasheet



Mors 1-5, 7151 MX Eibergen NL  
 www.rotor.nl tel.: +31 545 464640  
 sales@rotor.nl tel.: +31 545 464646

**Model No.** 2-Pole cage motor 6RN 90L 2,2kW D230V 50Hz IM2181-FT115

U (V)	Δ / Y Conn	f [Hz]	P		I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load			PF at __load			I <sub>A</sub> /I <sub>N</sub> [pu]	T <sub>A</sub> /T <sub>N</sub> [pu]	T <sub>R</sub> /T <sub>N</sub> [pu]
			[kW]	[hp]					FL	3/4FL	1/2FL	FL	3/4FL	1/2FL			
230	D	50	2,2	3	7,3	2920	7,2	IE3	85,9			0,88	0,85	0,78	8,20	2,60	4,00
400	Y				4,2												
265	D	60	2,55	3,418	7,3	3515	6,9	IE3	86,5	86,5	85,5	0,88			8,20	2,70	4,40
460	Y				4,21												

Motor type	<b>6RN90L02E34</b>
Enclosure	<b>Totally Enclosed Fan Cooling</b>
Frame Material	<b>Aluminum</b>
Frame size	<b>90L</b>
Duty	<b>S1</b>
Voltage	<b>230 V</b>
Frequency	<b>50 Hz</b>
Power output	<b>2,2 kW</b>
Insulation class	<b>F</b>
Ambient temperature	<b>-20 till 40 °C</b>
Temperature rise	<b>temp.rise acc. B (80K)</b>
Temperature rise winding	<b>38 K</b>
Temperature rise surface	<b>20 K</b>
Altitude above sea level	<b>1000 mtr</b>
Hazardous area classification	<b>Safe area</b>

Degree of protection	<b>IP55</b>
Mounting type	<b>IM2181-FT115</b>
Cooling method	<b>IC411</b>
Motor weight - approx.	<b>23 kg</b>
Gross weight - approx.	<b>24 kg</b>
Motor inertia	<b>0,0021 kgm<sup>2</sup></b>
Vibration level	<b>according IEC60034-14</b>
Noise level (pressure) acc 60034-9	<b>65 dB(A)</b>


Rotor type	<b>Cage motor</b>
Bearing type	<b>6004-2Z/C3WT</b>
Type of grease	<b>Unirex N3</b>
Phase resistance at 20°C	<b>2,6253 Ohm</b>
Country of origin	<b>CZ</b>

Voltage/Freq	Locked rotor Torque [nom] [%]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 230V 50Hz	260%	857%		400%	3,13 A
@ D 265V 60Hz	270%	819%	270%	440%	

**NOTE**

All performance values at rated voltage and frequency.  
 All performance parameters are subjected to standard tolerance as per IEC 60034-1  
 Voltage, Frequency are as per IEC60034-1  
 Technical data are subject to change. There may be discrepancies between calculated and name plate values.


Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30



6RN90L02E34 2-pole 2,20kW D/Y 230/400V 50Hz S1 IC411 IE3




Torque versus Speed curve with variable frequency drive



This is an uncontrolled copy - document subject to change - alterations reserved without notice

Therm\_VSD graph

This is an uncontrolled copy - document subject to change - alterations reserved without notice



Tn graph

