

PRODUCT INFORMATION PACKET



Model No: 6RN90S02E30U241081-Uni
Catalog No: 6RN90S02E30U24@1081-Uni

1.50 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 3000 rpm, D230/Y400V 50Hz,
90S Frame B3, IC411

Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	2 Hp	Output KW	1.5 kW
Frequency	50 Hz	Voltage	D230/Y400 V
Current	5.20 A	Speed	2910 rpm
Service Factor	1	Phase	3
Efficiency	84.5 %	Power Factor	0.86
Duty	S1	Insulation Class	F
Frame	90S	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6205-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6004-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	B3	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	24 mm	Shaft Extension	50 mm

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022

Model No. 2-Pole cage motor 6RN 90S 1,5kW D230V 50Hz IM1081

U (V)	Δ / Y Conn	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load FL 3/4FL 1/2FL			PF at __load FL 3/4FL 1/2FL			I _A /I _N [pu]	T _A /T _N [pu]	T _K /T _N [pu]
230	D	50	1,5	2	5,2	2910	4,9	IE3	85,2			0,86			8,10	2,70	4,20
400	Y				3												
265	D	60	1,75	2,346	5,15	3510	4,76	IE3	86,0			0,87			8,75	2,64	4,20
460	Y				2,95												

Motor type	6RN90S02E30
Enclosure	Totally Enclosed Fan Cooling
Frame Material	Cast iron
Frame size	90S
Duty	S1
Voltage	230 V
Frequency	50 Hz
Power output	1,5 kW

Insulation class	F
Ambient temperature	-20 till 40 °C

Temperature rise winding	38 K
Temperature rise surface	10 K
Altitude above sea level	1000 mtr
Hazardous area classification	Safe area

Rotor type	Cage motor
Bearing type	Rolling element bearing 6205-2Z/C3WT - 6004-2Z/C3WT

Type of grease	Unirex N3
----------------	-----------

Country of origin	CZ
-------------------	----

Torques	Locked rotor	At start	Pull-up	Breakdown	No-load
@230V 50Hz	270%	13,2 A	220%	420%	2,44 A
@265V 60Hz	264%	12,5 A	211%	420%	2,19 A

NOTE

All performance values at rated voltage and frequency.
All performance parameters are subjected to standard tolerance as per IEC 60034-1
Voltage, Frequency are as per IEC60034-1
Technical data are subject to change. There may be discrepancies between calculated and name plate values.


Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30

Degree of protection	IP55
Mounting type	IM1081
Cooling method	IC411
Motor weight - approx.	16 kg
Gross weight - approx.	16 kg
Motor inertia	0,0021 kgm²

Vibration level	according IEC60034-14
-----------------	-----------------------

Starting method	d.o.l.
Direction of rotation	cw /ccw
Paint shade	RAL 7030

Terminal box position	Top - Pos 3
-----------------------	-------------




This is an uncontrolled copy, data can be changed anytime.




6RN90S02E30 2-pole 1,50kW D/Y 230/400V 50Hz S1 IC411 IE3



Torque versus Speed curve with variable frequency drive



Therm_VSD graph



Tn graph

