

# PRODUCT INFORMATION PACKET

rotor nl®

Model No: 6RN80M04E32U24B2181-A

Catalog No: 6RN80M04E32U24B@2181-A

0.55 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 1500 rpm, D230/Y400V 50Hz,  
80M Frame B34, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord®



### Nameplate Specifications

Output HP	0.75 Hp	Output KW	0.55 kW
Frequency	50 Hz	Voltage	D230/Y400 V
Current	2.17 A	Speed	1440 rpm
Service Factor	1	Phase	3
Efficiency	80.8 %	Power Factor	0.77
Duty	S1	Insulation Class	F
Frame	80M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6204-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6004-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

### Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	B34	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	19 mm	Shaft Extension	40 mm
Outline Drawing	6RN80M04E32_2141-A		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023

## Datasheet


**rotor** B.V.

Mors 1-5, 7151 MX Eibergen NL

www.rotor.nl tel.: +31 545 464640

sales@rotor.nl tel.: +31 545 464646

Model No. 4-Pole cage motor 6RN 80M 0,55kW D230V 50Hz IM2181-FT100

U (V)	$\Delta / Y$	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load FL 3/4FL 1/2FL	PF at __ load FL 3/4FL 1/2FL	I <sub>A</sub> /I <sub>N</sub> [pu]	T <sub>A</sub> /T <sub>N</sub> [pu]	T <sub>R</sub> /T <sub>N</sub> [pu]
230	D	50	0,55	0,737	2,17	1440	3,65	IE3	81,5 81,8 79,9	0,77 0,69 0,56	6,03	2,13	3,10
400	Y				1,25								
265	D	60	0,63	0,845	2,13	1740	3,46	IE3	83,3 83,5 81,5	0,77 0,69 0,57	6,43	2,40	3,30
460	Y				1,23								

Motor type	6RN80M04E32	Degree of protection	IP55
Enclosure	Totally Enclosed Fan Cooling	Mounting type	IM2181-FT100
Frame Material	Aluminum	Cooling method	IC411
Frame size	80M	Motor weight - approx.	12 kg
Duty	S1	Gross weight - approx.	12 kg
Voltage	230 V	Motor inertia	0,0021 kgm <sup>2</sup>
Frequency	50 Hz	Vibration level	according IEC60034-14
Power output	0,55 kW	Noise level (pressure) acc 60034-9	50,3 dB(A)
Insulation class	F		
Ambient temperature	-20 till 40 °C		
Temperature rise	temp.rise acc. B (80K)		
Temperature rise winding	23 K		
Temperature rise surface	17 K	Direction of rotation	cw /ccw
Altitude above sea level	1000 mtr		
Hazardous area classification	Safe area		

Rotor type	Cage motor
Bearing type	6004-2Z/C3WT
Type of grease	Unirex N3
Phase resistance at 20°C	27,0390 Ohm
Country of origin	CZ

Voltage/Freq	Locked rotor Torque [% nom]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 230V 50Hz	213%	603%	210%	310%	1,32 A
@ D 265V 60Hz	240%	643%	204%	330%	1,23 A

NOTE	All performance values at rated voltage and frequency. All performance parameters are subjected to standard tolerance as per IEC 60034-1 Voltage, Frequency are as per IEC60034-1 Technical data are subject to change. There may be discrepancies between calculated and name plate values.	Schematic presentation of torque-speed curve
Efficiency Europe	Global IEC	
Standards EN-IEC: 60034-30	IEC: 60034-30	


This is an uncontrolled copy, data can be changed anytime.

**rotor**  
 is a  
**ISO 9001**  
 certified  
 company


6RN80M04E32 4-pole 0,55kW D/Y 230/400V 50Hz S1 IC411 IE3



Torque versus Speed curve with variable frequency drive



Therm\_VSD graph



Tn graph

