


PRODUCT INFORMATION PACKET



Model No: 6RN90L06E34U24B3042

Catalog No: 6RN90L06E34U24B@3042

1.10 kW General Purpose Low Voltage IEC Motor IE3, 3 phase, 1000 rpm, D230/Y400V 50Hz,
90L Frame B5, IC411



Regal and Rotor nl are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1.50 Hp	Output KW	1.1 kW
Frequency	50 Hz	Voltage	D230/Y400 V
Current	4.95 A	Speed	945 rpm
Service Factor	1	Phase	3
Efficiency	81 %	Power Factor	0.69
Duty	S1	Insulation Class	F
Frame	90L	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6205-2Z/C3WT (-40°C/+160°C)	Opp Drive End Bearing Size	6004-2Z/C3WT (-40°C/+160°C)
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	6	Rotation	Clockwise Shaft End
Mounting	B5	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	24 mm	Shaft Extension	50 mm
Outline Drawing	6RN90L06E34_3041		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022

Datasheet

rotor nl®

rotor b.v.

Mors 1-5, 7151 MX Eibergen NL
www.rotor.nl tel.: +31 545 464640
sales@rotor.nl tel.: +31 545 464646

Model No. 6-Pole cage motor 6RN 90L 1,1kW D230V 50Hz IM3042-FF165

U (V)	Δ / Y Conn	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [Nm]	IE Class	% EFF at __ load FL 3/4FL 1/2FL	PF at __ load FL 3/4FL 1/2FL	I _A /I _N [pu]	T _A /T _N [pu]	T _K /T _N [pu]
230	D	50	1,1	1,5	4,95	945	11,1	IE3	79,2 80,1 78,7	0,69 0,60 0,47	4,66	2,30	2,70
400	Y				2,86								
265	D	60	1,27	1,702	5,31	1145	10,6	IE1	81,9 82,7 81,4	0,69 0,61 0,48	4,87	2,16	2,79
460	Y				3,07								

Motor type	6RN90L06E34
Enclosure	Totally Enclosed Fan Cooling
Frame Material	Aluminum
Frame size	90L
Duty	S1
Voltage	230 V
Frequency	50 Hz
Power output	1,1 kW
Insulation class	F
Ambient temperature	-20 till 40 °C
Temperature rise	temp.rise acc. B (80K)
Temperature rise winding	44 K
Temperature rise surface	
Altitude above sea level	1000 mtr
Hazardous area classification	Safe area

Rotor type	Cage motor
Bearing type	6205-2Z/C3WT - 6004-2Z/C3WT

Type of grease	Unirex N3
----------------	-----------

Phase resistance at 20°C	5,6053 Ohm
Country of origin	CZ

Voltage/Freq	Locked rotor Torque [% nom]	Starting current [% nom]	Pull-up Torque [% nom]	Breakdown Torque [% nom]	No-load Current [A]
@ D 230V 50Hz	230%	466%	224%	270%	3,29 A
@ D 265V 60Hz	216%	487%	218%	279%	3,08 A

NOTE

All performance values at rated voltage and frequency.

All performance parameters are subjected to standard tolerance as per IEC 60034-1

Voltage, Frequency are as per IEC60034-1

Technical data are subject to change. There may be discrepancies between calculated and name plate values.


Efficiency	Europe	Global IEC
Standards	EN-IEC: 60034-30	IEC: 60034-30

This is an uncontrolled copy, data can be changed anytime.

Degree of protection	IP55
Mounting type	IM3042-FF165
Cooling method	IC411
Motor weight - approx.	21 kg
Gross weight - approx.	22 kg
Motor inertia	0,0048 kgm²
Vibration level	according IEC60034-14
Noise level (pressure) acc 60034-9	57 dB(A)

Direction of rotation	cw /ccw
-----------------------	---------

Schematic presentation of torque-speed curve




rotor
is a
ISO 9001
certified
company

RegalRexnord


6RN90L06E34 6-pole 1,10kW D/Y 230/400V 50Hz S1 IC411 IE3



Torque versus Speed curve with variable frequency drive



Therm_VSD graph



Tn graph

