



Nameplate Specifications

| | | | |
|------------------------|------------|----------------------------|-----------------------------|
| Output HP | 75 Hp | Output KW | 56.0 kW |
| Frequency | 60 Hz | Voltage | 460 V |
| Current | 84.0 A | Speed | 3555 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Efficiency | 94.5 % | Power Factor | 88.5 |
| Duty | Continuous | Insulation Class | F |
| Design Code | B | KVA Code | G |
| Frame | 365TS | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6312 | Opp Drive End Bearing Size | 6312 |
| UL | Recognized | CSA | Y |
| CE | Y | IP Code | 56 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|------------------------------|-----------------------|------------------|
| Electrical Type | Squirrel Cage Inverter Rated | Starting Method | Line Or Inverter |
| Poles | 2 | Rotation | Reversible |
| Resistance Main | .07 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Cast Iron |
| Shaft Type | TS | Overall Length | 30.38 in |
| Frame Length | 14.50 in | Shaft Diameter | 1.875 in |
| Shaft Extension | 3.75 in | Assembly/Box Mounting | F1/F2 CAPABLE |
| Outline Drawing | B-SS508654LE-1450 | Connection Drawing | A-EE7300U-LE |