



Nameplate Specifications

Output HP	15 Hp	Output KW	11.2 kW
Frequency	120 Hz	Voltage	460 V
Current	18.0 A	Speed	1800 rpm
Service Factor	1	Phase	3
Efficiency	94 %	Power Factor	80
Duty	Continuous	Insulation Class	H
Design Code	No Design Code	KVA Code	N/A
Frame	254TC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Thermostats 140 deg. C (N/C)	Ambient Temperature	40 °C
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6210
UL	Recognized	CSA	Y
CE	Y	IP Code	54
Number of Speeds	1		

Technical Specifications

Electrical Type	AC Permanent Magnet	Starting Method	Inverter Only
Poles	8	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Outline Drawing	B-SS203152-1225	Connection Drawing	A-EE7300T

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/26/2021