

Nameplate Specifications

Output HP	25 Hp	Output KW	18.7 kW
Frequency	60 Hz	Voltage	208-240/380-415/440-480 V
Current	58.0-56.0/36.0-33.0/ A	Speed	3520 rpm
Service Factor	1	Phase	3
Efficiency	91 %	Power Factor	88.3
Duty	Continuous	Insulation Class	H
Design Code	B	KVA Code	G
Frame	256TCVZ	Enclosure	Open Enclosed
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	309	Opp Drive End Bearing Size	206
UL	Recognized	CSA	Y
CE	Y	IP Code	10
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	.365 Ohms	Mounting	Round
Motor Orientation	Horizontal Or Shaft Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Connection Drawing	A-EE7358D	Outline Drawing	B-SS89315LE-1240