



Nameplate Specifications

| | | | |
|------------------------|-------------------|----------------------------|----------------------------------|
| Output HP | 15 Hp | Output KW | 11.2 kW |
| Frequency | 60 Hz | Voltage | 460 V |
| Current | 18.2 A | Speed | 1770 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Efficiency | 92.4 % | Power Factor | 83 |
| Duty | Continuous | Insulation Class | H |
| Design Code | B | KVA Code | G |
| Frame | 254T | Enclosure | Totally Enclosed Air Over |
| Thermal Protection | No | Ambient Temperature | 90 °C |
| Drive End Bearing Size | 6309 | Opp Drive End Bearing Size | 6210 |
| UL | Recognized | CSA | Y |
| CE | Y | IP Code | 54 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|-------------------------------------|-----------------------|-------------------------------|
| Electrical Type | Squirrel Cage Inverter Rated | Starting Method | Line Or Inverter |
| Poles | 4 | Rotation | Reversible |
| Resistance Main | .6 Ohms | Mounting | Rigid Base |
| Motor Orientation | Horizontal | Drive End Bearing | Ball / Heat Stabilized |
| Opp Drive End Bearing | Ball / Heat Stabilized | Frame Material | Cast Iron |
| Shaft Type | T | Overall Length | 20.83 in |
| Frame Length | 10.50 in | Shaft Diameter | 1.625 in |
| Shaft Extension | 4 in | Assembly/Box Mounting | F1/F2 CAPABLE |
| Inverter Load | VARIABLE 20:1 | | |
| Connection Drawing | A-EE7300T-LE | Outline Drawing | B-SS203092-1050 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021