



Nameplate Specifications

Output HP	7 1/2 Hp	Output KW	5.6 kW
Frequency	60 Hz	Voltage	230 V
Current	29.5 A	Speed	3520 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Frame	213JMZ	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Mounting	Special/Non-Standard	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	7/8 Keyed
Overall Length	19.92 in	Frame Length	11.15 in
Shaft Diameter	1.000 in	Shaft Extension	4.25 in
Outline Drawing	OLCEQ750	Connection Drawing	EE9048MF-CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022