

# PRODUCT INFORMATION PACKET



Model No: CEQK1500  
Catalog No: CEQK1500  
15.0 HP Pool Pump Motor, 3 phase, 3600 RPM, 230/460 V, 215JMZ Frame, ODP  
Pool Pump Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications

Output HP	15.0 Hp	Output KW	11.2 kW
Frequency	60 Hz	Voltage	230/460 V
Current	36.5/18.2 A	Speed	3525 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	215JMZ	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

### Technical Specifications

Electrical Type	Polyphase	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Special/Non-Standard	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	7/8 Keyed
Overall Length	19.78 in	Frame Length	11.15 in
Shaft Diameter	1.000 in	Shaft Extension	4.25 in
Connection Drawing	005010.01CY	Outline Drawing	OLCEQK1500

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021




VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



## LINE LEADS



VOLTAGE	L1	L2	L3	JOIN & INSULATE
HIGH	T1	T2	T3	(T4,T7) (T5,T8) (T6,T9)
LOW	T1,T7	T2,T8	T3,T9	T4,T5,T6

				TOLERANCES UNLESS SPECIFIED			DRAWN GR 03/27/12		
				DEC.	INCHES		CHK ST 03/27/12		
				.X	±.1		APPD		
				.XX	±.01		SCALE 1=1		
				.XXX	±.005	TITLE EXTERNAL WIRING DIAGRAM 3 PHASE W/O PROTECTOR		REF 005010-01	
				.XXXX	±.0005	MAT'L. DECAL - 004014		FMF	
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"	FINISH		PREV	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT			RFP		CAD FILE 00501001CY		SIZE	DRAWING NO.	REV.
			DIST BRF-NLV				A	005010-01CY	