



Nameplate Specifications

Output HP	7 1/2 Hp	Output KW	5.6 kW
Frequency	60 Hz	Voltage	230/460 V
Current	17.8/8.9 A	Speed	3490 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	184JMZ	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Polyphase	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Special/Non-Standard	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Steel	Shaft Type	7/8 Keyed
Overall Length	17.61 in	Frame Length	11.00 in
Shaft Diameter	1.000 in	Shaft Extension	4.25 in
Connection Drawing	005010.01CY	Outline Drawing	OLCEQK750

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021