



### Nameplate Specifications

|                    |               |                     |                             |
|--------------------|---------------|---------------------|-----------------------------|
| Output HP          | 1.5 Hp        | Output KW           | 1.1 kW                      |
| Frequency          | 60 Hz         | Voltage             | 208-230/460 V               |
| Current            | 4.4-4.0/2.0 A | Speed               | 3485 rpm                    |
| Service Factor     | 1.15          | Phase               | 3                           |
| Duty               | Continuous    | Insulation Class    | F                           |
| Frame              | 143JP         | Enclosure           | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C                       |
| UL                 | Recognized    | CSA                 | Y                           |
| Number of Speeds   | 1             |                     |                             |

### Technical Specifications

|                       |            |                   |                 |
|-----------------------|------------|-------------------|-----------------|
| Electrical Type       | POLYPHASE  | Starting Method   | Across The Line |
| Poles                 | 2          | Rotation          | Reversible      |
| Mounting              | Rigid Base | Drive End Bearing | Ball            |
| Opp Drive End Bearing | Ball       | Frame Material    | Cast Iron       |
| Shaft Type            | Keyed      | Overall Length    | 18.70 in        |
| Frame Length          | 5.75 in    | Shaft Diameter    | 1.156 in        |
| Shaft Extension       | 7.31 in    |                   |                 |
| Connection Drawing    | A-EE7308   | Outline Drawing   | SS620616        |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022