



Nameplate Specifications

| | | | |
|--------------------|------------|---------------------|-----------------|
| Output HP | 5 Hp | Output KW | 3.7 kW |
| Frequency | 60 Hz | Voltage | 575 V |
| Current | 5.1 A | Speed | 3495 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Duty | Continuous | Insulation Class | F |
| Frame | 182J | Enclosure | Open Drip Proof |
| Thermal Protection | None | Ambient Temperature | 40 °C |
| UL | Recognized | CSA | Y |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|------------|-------------------|-----------------|
| Electrical Type | POLYPHASE | Starting Method | Across The Line |
| Poles | 2 | Rotation | Reversible |
| Mounting | Rigid Base | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | Keyed | Overall Length | 17.70 in |
| Frame Length | 7.26 in | Shaft Diameter | 1.249 in |
| Shaft Extension | 7.31 in | | |
| Connection Drawing | EE7308 | Outline Drawing | SS600205 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021