



Nameplate Specifications

Output HP	5.0 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	230 V
Current	22.2 A	Speed	3501 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Frame	184JMZ	Enclosure	Drip Proof
Thermal Protection	Manual	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Mounting	Special/Non-Standard	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	7/8 Keyed
Overall Length	17.11 in	Frame Length	10.50 in
Shaft Diameter	1.000 in	Shaft Extension	4.25 in
Connection Drawing	005056.03CY	Outline Drawing	OLCEQ500

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021