



### Nameplate Specifications

Output HP	7 1/2 Hp	Output KW	5.6 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	19-17/8.5 A	Speed	3510 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	184JM	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

### Technical Specifications

Electrical Type	POLYPHASE	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	17.37 in
Frame Length	7.75 in	Shaft Diameter	1.000 in
Shaft Extension	4.26 in		
Connection Drawing	A-EE7308	Outline Drawing	SS620311

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021